

□□□□□

\*. 3 □□□ □□□□□□ □□□□ □□□□ □□□□ 1 □□ 3 □□□□□□□□ 755 □□□□□□□□ 808 □□□□□□□□ 1064 □□□□ 1000 □□□□ □□□□ :□□□□ □□□□W/1200W/1600W □□ □□□□ □□□□

\* □□□ □ □□□□ □□□□ □□□□ □□□ □□□□ □□□□ □□□□ 35\*12 □□□□ □□□□ 20\*12 □□□□ □□□□!

\*. □□□ □□ □□□□□ □□□□□ □□□ □□□□□ :□□□□□ □□□ □□□□□ Dual-TEC □□ □□□□□□□ □□□□ □□□□□□□□ □□□ □□□□□□□□ 40 :□□□□ □□□□.\* .□□□□□□□ □□□□ □□□□ □□□□ 24 □□□□ □□□ □□□□ □□ □□□□□□ □□□□

\*.□□□□ □□□□ □□ □□□□ □□□□.

\* 40,000,000 □□ □□□□□ □□□ □□□ □□ □□□□□ □□□□□□ □□ □□□□□ □□□□□ □□□□ □□□□ □□□□ □□□□.

\* □□□□□□ □□□□ □□□□ □□□□□□□□

\*.□□□ □ □□□□ □□□□□ □□□□ □□□□ □□□ □□□□

\*.14.0 □□□□ □□□□ 6 □□ □□□□□ □□□□ □□□□ □□□□□ □□□□ □□□□□.



### What is diode laser hair removal?


Alma soprano xl titanium Diode laser hair removal comes with 808nm wavelength laser stack or 755+808+1064 triple wavelength laser stack with semiconductors technology. They are assembled together to produce light for permanent hair removal/hair reduction/depilation/epilation treatment!



Emit a laser beam



The laser beam is absorbed by hair follicle melanin



Different color hair has different ability to absorb light wave



After absorption, the laser energy will be converted into heat energy



Hair follicles and surrounding stem cells lose their activity and fall off



So reach hair removal effect




7558081064 (12\*20mm) (12\*35mm)nm.  
 3 (12\*20mm) (12\*35mm) (12\*20mm) (12\*35mm):  
 755 (12\*20mm) (12\*35mm) (12\*20mm) (12\*35mm)  
 808nm (12\*20mm) (12\*35mm) (12\*20mm) (12\*35mm)  
 1064 (12\*20mm) (12\*35mm) (12\*20mm) (12\*35mm)

# Treatment effect

## Suit to any color of skin



## Before&After



این روش برای هر نوع پوستی مناسب است و نتایج آن ماندگار است. همچنین این روش برای درمان مشکلاتی مانند آکنه، جوش و منافذ گشاد نیز مؤثر است.

## BEFORE AND AFTER TREATMENT

MAKE YOUR SKIN SILKY AND FULL OF CHARM!

