

NEW ARRIVALS

2022 Newest Permanent and Painless Ice Hair Removal

- 3 waves 1064nm+808nm+755nm,
- 3 in 1 all skin type can be used
- Imported gold laser bar, Shots up to 40 million+



12*20mm



12*35mm



* (1064nm 808nm 755nm 3 waves) .3 waves 1064nm+808nm+755nm .3 in 1 all skin type can be used .Imported gold laser bar, Shots up to 40 million+
1064 808 755 *nm 3 waves 1064nm+808nm+755nm .3 in 1 all skin type can be used .Imported gold laser bar, Shots up to 40 million+

Newest Factory Lowest Price Diode Laser Hair Removal

A new
winner
is born!



HD 4K Screen Design

The screen
can be rotated for
more convenient
operation

One-touch
start button

000000 000 00000 24 000 00000 00000 0000 000 00000000000 0000 31.3- 00 000000 2 000000 00000 00000 0000 0000 0000

ULTRA-LOW Temperature -31°C

Ultra low temperature
protect skin
not burned by the laser

00 0000000 000000 000

* 000 00 000 00 00000 000000 000000 0000 00 000 0000000000 000000 00000 000 00 00000000

* 00 0000000 00000 0000 0000 0000 0000000 0000

0000000 00 0000 00000 00 0000 0000 *

MULTI-ANGLE MACHINE DISPLAY

New upgrade 14-inch HD 4K screen

The screen can be rotated 180 degrees

12*35mm big spot size

Optional parameters for different skin types



*.3 1000 1200W/1600W//1800W 1 3 755 808 1064 :1000

*.1000 1200W/1600W//1800W 1 3 755 808 1064 :1000

*.36*12 24*12 24*12 24*12 24*12 24*12 24*12 24*12 24*12 24*12

*. Dual-TEC 24 24 24 24 24 24 24 24 24 24

*.40 :40 40

Three Simultaneous Wavelengths in one Applicator

12mm*20mm / 12mm*35

4cm²

Mix Laser 755nm+808nm+1064nm
Multiple Laser Wavelengths and Technologies

Alex 755nm
Ideal for range of hair colors

Speed 808nm
Safe for darker skin types

YAG 1064nm
Perfect solution for darker skin

이러한 레이저는 피부의 색소 침착, 모발, 그리고 혈관을 표적으로 하여 다양한 피부 문제를 해결할 수 있습니다. 또한, 레이저는 피부의 콜라겐 생성을 자극하여 피부 탄력을 향상시키고 주름을 줄이는 데도 효과적입니다.

Simple installation and easy handling of areas that are usually difficult to reach

12x24mm 1200W big power

Improved Reach: 360° Rotatable

Easy installation

Finger treatment

Nose hair treatment

Ear treatment

Eyebrow treatment

이러한 레이저는

□□□□□□ □□ □□□□ □□□□ □□□□□□□□

□□□□□□ □□□□□□ □□□ □□□□ □□□□□ □□□□□ □□ □□ □ □□□ □□□□ □□□□ □□□ □□□□ □□□□.

በሥነ ምግባር ምርት ስርዓት ለማረጋገጥ የሚያስፈልጉትን ሰነዶች በጊዜ ላይ ለማቅረብ ይችላሉ፡፡ 40 ሰዓት ይዟል፡፡

000000 00 00000000 00 000000 000 00000 00 00 000 00000 000000 000 000 0 000 00000000



□□ □□□□ □□□□ □□□□ □□□□ □□□□ □□□□ □□□□ □□□□

□□□ □□□□□ □□□□ □□□□ □□□□ □□□□ 3 □□ □□.

* □□□□ □□□□ □□□□ * □□□□ □□□□ * □□□□ * □□□ □□□□



1064 808 755 □□□□ □□□□ □□□□ 14 □□□□ □□□□ □□□□ □□□□

[illegible]

*□□□□□ □□ □□ □□□□□ □□

* □□□□□ □□□ □□□□□

* □□□□□□ □□□□□□ □□□□ □□□□□□

OEM / ODM 我們提供 OEM 和 ODM 服務

○○○○○ ○○○ ○○○○○○ ○○○○ ○○○○○ ○○○○○○!