



MLKJ LIFETIME SERVICE

**FIRST COMPANY THAT OFFERED 2 YEARS WARRANTY**

START SERVICE

1

 **24-Hour online**  
After-sales service

 **15 Years Laser Beauty**  
Device Manufacturer

 **OEM Factories**  
Support customization

□□ □□□□ □□□□ □□□□ □□□□ □□□□□□ □□ □□ □□ □□□□ □□□□.

EXFU Seiko



# 11D HIFU

Macro & Micro High Intensity Focused Ultrasound System



SAFE



EFFECTIVE




MULTI-DEPTH



11 EXFU Seiko 11D HIFU Macro & Micro High Intensity Focused Ultrasound System

EXFU Seiko 11D HIFU






**Macro & Micro High Intensity Focused Ultrasound System**

# 7 CARTRIDGES + 4 GUN HEADS

1.5mm, 2.0mm, 3.0mm, 4.5mm for face treatment  
 6.0mm, 9mm, 13mm for body treatment.


This system is designed for non-invasive skin tightening and lifting. It uses high-intensity focused ultrasound (HIFU) energy to stimulate collagen production and contract existing collagen fibers in the skin. The system is suitable for treating the face, neck, and body. The treatment is performed using a handheld device with a cartridge containing the HIFU transducer. The system is easy to use and does not require anesthesia. The results are visible immediately and can last for several months. The system is also suitable for treating wrinkles and sagging skin. The treatment is performed using a handheld device with a cartridge containing the HIFU transducer. The system is easy to use and does not require anesthesia. The results are visible immediately and can last for several months. The system is also suitable for treating wrinkles and sagging skin.




## MF2.0MM

Unique ultra-thin  
probe Clexis patented  
technology

"Special cartridge for eyes treatment"



# Body Treatment



## • *Treatment Effect* •



□□□	□□□□□□ □□□□ 7 □□□□□□ □□ □□□□□□ □□□□□□□□□□
□□□	□□□□□ □□□ □□ □□□□□□ □□□□□□□□□□

RF 4.5MHz / MF 3.0MHz / LF 1.5MHz	7D HF: MF2/6/9/13 L4-4.5 L7-1.5 L7-3.0
RF Power	0.1J-2.5J (0.1J 0.5J 1.0J 1.5J 2.0J 2.5J)
RF Tip	1.0mm-4.0mm
RF Mode	5-25 sec
RF Count	300000
RF Tip Size	15mm
RF Power	110V-240V 50/60Hz



- 1. 15.6 inch touch screen
  - 2. 6 touch points
  - 3. OEM (OEM/ODM)
  - 4. OEM (OEM/ODM)
- EXFU Seiko is a professional beauty device manufacturer!