

New Machine

“

**High power diode laser
with nice cooling technology**
for hair removal with painless!

”




* 1800 Watts power laser!

* The machine has a large cooling system that keeps the skin cool during the treatment. The machine has a large cooling system that keeps the skin cool during the treatment. The machine has a large cooling system that keeps the skin cool during the treatment.

* The machine has a large cooling system that keeps the skin cool during the treatment. The machine has a large cooling system that keeps the skin cool during the treatment. The machine has a large cooling system that keeps the skin cool during the treatment.


* The machine has a large cooling system that keeps the skin cool during the treatment. The machine has a large cooling system that keeps the skin cool during the treatment. The machine has a large cooling system that keeps the skin cool during the treatment.



755 nm for white skin (fine, golden hair removal);



808 nm for yellow neutral skin (brown hair removal);



1064 nm for black skin (black hair removal)

□□□□ □□□□□□□□

1. □□□□□ □□□ □□□ □□ □□□□□ □□□□□ □□ □□□□□ □□□□□□□□□□
2. □□□□ □□□ □□ □□□□ □□□□□
3. 40,000,000 □□□□□ □□□□ □□ □□ □□□□ □□□□ □□□□ □□□□ □□□□ □□□□
4. □□□□□ □□□□ □□□□ □□□□□ □□□□□
5. 14.0 □□□□□ □□□ □□□□□
6. □□□□□ □□□ □□□□□

Handle Details

Three Wavelengths Work Togher



1064 808 755

755 .() 808nm .() 1064).

For all skin types

Triple wavelength laser work together

755
nm

808
nm

1064
nm

755nm/808nm/1064nm

755nm
808nm
1064nm

Laser hair removal treatment theory



Hair active growth
phase(3-6years)



laser treatment



Transition phase
(1-2weeks)



Resting phase
(1-2 weeks)



Return to growth
phase

□□□□□ □□□□□□□□□□□□







型番	808V29
照射波長	755/808/1064 nm 3波長
冷却方式	808nm 冷却ファン
冷却面積	400cm ² 14段階調整可能
冷却速度	755/808/1064nm
冷却時間	20-40分
冷却パワー	10~150 J/cm ²
冷却周波数	1-10Hz
冷却モード	冷却ファン
冷却速度	3500 J/min
冷却面積	12*24mm 36*12 mm
冷却時間	110分
冷却パワー	50 / 220 J
冷却周波数	60 / 105 Hz
冷却モード	53*40*105 mm

□□□ □ □□□ □□□ □□□□□□



00000 000000 00 00 0 00000000 00 0000 00000 !000000 000000 00000 00000 00000 000000 0000!
 000000 00000 000000 000000
 00000 000000

- * 14.0 14.0
- * 14.0 14.0
- * 14.0 14.0
- * 14.0 14.0

Custom Section

LOGO design



SYSTEM design



LOGO design

SYSTEM design

LOGO design

Our customers

60000+ CUSTOMERS



102

Countries

OEM/ODM

Customize the machine according to customer needs

CERTIFICATE



14 我们拥有 102 个国家 10000 多个客户 60000+ 客户！

13 我们拥有 102 个国家 10000 多个客户 60000+ 客户

我们拥有 102 个国家 10000 多个客户 60000+ 客户 CE 认证 TUV 认证

我们拥有 102 个国家 10000 多个客户 60000+ 客户 OEM

我们拥有 102 个国家 10000 多个客户 60000+ 客户

我们拥有 102 个国家 10000 多个客户 60000+ 客户 我们拥有 102 个国家 10000 多个客户 60000+ 客户

我们拥有 102 个国家 10000 多个客户 60000+ 客户

PACKING

Safe and thoughtful packaging service



Built-in prevention
collision bubble

Two- year warranty for machine
handle as consumable,
one-year warranty

Tight packaging

Training:
(video +manual+online service)
can keep you operate it easily



3-5 business days
delivery

professional guide:
24 hours professional online
customer service