



New Style Diode Laser

Painless, permanent hairremoval

..... 24

350g lightweight **handle**, more ergonomic

Available in **black or white**



1064 808 755 □□□□ □□□□ □□□□ □□□□ □□□□ □□□□□□

□□□ 1000 □□□□ 10 □□□□ □□□□ 20 * 12 □□□□ □□□□□□.

.000 1200 0000 12 0000 0000 35 * 12 0000 000000

1600 16 35 * 12

[illegible]

0000 000000 000 000000 00000



12*24mm 1200W handle
Additional therapeutic head



12*36mm 1800W handle
Additional therapeutic head



1064 808 755 [www.essio.com](#) [www.essio.com](#) [www.essio.com](#) [www.essio.com](#) [www.essio.com](#)

- 1) [www.essio.com](#) [www.essio.com](#) [www.essio.com](#) [www.essio.com](#) [www.essio.com](#)
- 2) [www.essio.com](#) [www.essio.com](#) [www.essio.com](#) [www.essio.com](#) [www.essio.com](#)
- 3) [www.essio.com](#) [www.essio.com](#) [www.essio.com](#) [www.essio.com](#) [www.essio.com](#)




□□□□ □□□□

1. □□□□ □□□□ □□□□ 14 □□□ □□□ □□□□ □□□□
2. □□□□ □□□□ □□□□ □□□ □□□ □□□□ □□□□ □□□□

.3 .
 OEM (/ ...)

The new 14-inch 4K screen

Support system customization



Technical Specifications

Wavelength	755 nm808nm1064nm
Spot size	16 --- 8 mm
Spot depth	100 mm
Spot width	14 mm
Spot height	808nm 808 nm755nm1064nm
Spot area	12 * 35 mm 20 * 12 / mm
Spot power	808 40000000-10000000 J/cm2 :J/cm2
Spot frequency	10-150 J / cm2 150 (J/cm2)
Spot pulse	40 ~ 800 ms
Spot pulse	1.0-10 ms
Spot pulse	TEC TEC TEC TEC
Spot pulse	800w/1000w/1200w/1600w
Spot pulse	2000 ms
Spot pulse	220 mm 60 / mm 110 mm 50 / mm
Spot pulse	-10 ~ 3 mm
Spot pulse	27 mm 31 mm
Spot pulse	AC220V/110V 50~60Hz

□□□□ □□ □□□□□ □ □□□□□ □□□□ □□□□□ □□□□!