

Why

choose us?

14 years factory

14 years of focus on the development of beauty equipment, the pursuit of higher product quality, making beauty entrepreneurship easier


60000+ customers in 102 countries

The products are sold to 102 countries, serving more than 60,000+ customers

2 years warranty

2 years warranty for each machine All question will be response within 24 hours solved within 72 hours

Make Your Beauty Business More Easier !



1. 14 years factory

14 years of focus on the development of beauty equipment, the pursuit of higher product quality, making beauty entrepreneurship easier A.ODM / OEM B. 14 years of focus on the development of beauty equipment, the pursuit of higher product quality, making beauty entrepreneurship easier C. 14 years of focus on the development of beauty equipment, the pursuit of higher product quality, making beauty entrepreneurship easier CE ISO 13485 D. 14 years of focus on the development of beauty equipment, the pursuit of higher product quality, making beauty entrepreneurship easier

2. 60000+ customers in 102 countries

DIODE LASER

*3 waves 1064nm +808nm + 755nm,
*Safe, Fast, Painless, permanent
*For all skin and hair style hair removal

>>>

1. 14 years factory

2. 40,000,000 customers in 102 countries

3. 2 years warranty

4. 14 years of focus on the development of beauty equipment, the pursuit of higher product quality, making beauty entrepreneurship easier

0000 000 6 00 00000 5.14.0 00000 0000 0000 00000 0000.

Machine display

Show the machine from three angles, looking at the machine comprehensively.




MACHINE DETAILS DISPLAY

EXQUISITE DETAIL DISPLAY



□□□□ □□□□□



- **755nm for white skin** (fine, golden hair removal)
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)


□□□□ □□□□□□□□□□



□□□ □□□□ □□□ 10-300ms □□□□□ □□□□□
 □□□□□□□ □□□□ -27℃~5℃
 □□□□ □□□□ 10bar/12bar/16bar□□□□□□□ □□□□□ □□□□□/□□□□□ □□ □□□□□□□□
 □□□□ □□ □□□□□□□□ 7558081064 □□□□□□ □□□□□ □□□□□□□
 □□□□□ □□□□ 1000w/1200w/1600w
 □□□□ □□□ □□□□□□□□□□ 755/808/1064 □□□□ 3 □□ □□□□□□□□□□ 808 □□□□□□ □□□□□
 □□□□□ □□□□□ □□□□□□□ 12 □□□□□ □□□□□
 □□□□ □□□□ 755/808/1064

時間 20-40 分鐘 時間
 脈寬 10~150 j/cm2 脈寬 脈寬
 脈頻 1-10 脈頻
 脈波 脈波 脈波
 脈波 3500 脈波
 脈波 脈波 12 * 20 脈波 脈波 35 * 12 脈波 脈波
 脈波 110 脈波 脈波 50 / 脈波 220 脈波 脈波 60 / 脈波
 脈波 脈波 95 脈波 脈波
 脈波 脈波 53*40*105 脈波 脈波

脈波 脈波 脈波



脈波 脈波

1. 脈波 脈波 脈波 脈波 脈波 脈波 6 脈波 脈波 6 脈波 脈波 .2 脈波 脈波 脈波 脈波 14 脈波 脈波 脈波 脈波 脈波 脈波 脈波 .4 脈波 脈波 脈波 脈波 脈波 脈波 脈波 脈波 脈波 脈波 6 .3 OEM (脈波/脈波...)

脈波 脈波 脈波 脈波 脈波 脈波 脈波 脈波

