



0000000 0000000







## Multi-angle display



### Specification

- High-quality IPL handpiece with super cooling system
- Optional Spot Size 15\*50mm, 15\*35mm, 12\*30mm
- Long shots time:  
IPL: 150,000 times
- 7 filters: 420/510/560/585/640/690/755nm  
Standard: 420/510/560/690nm

### Cooling Effect

The handle adopts a refrigeration effect which can effectively cool the skin in the treatment process and improve the comfort of treatments.


large  
area

Cool  
painless  
comfortable



Protect  
surrounding  
skin

Fast  
hair  
removal

## Filters for choice



ABS plastic filter box,  
more exquisite, more durable

|                                                                                   |                                                                                   |                                                                                   |                                                                                   |                                                                                    |                                                                                     |                                                                                     |
|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|  |  |  |  |  |  |  |
| 420nm                                                                             | 510nm                                                                             | 560nm                                                                             | 585nm                                                                             | 640nm                                                                              | 690nm                                                                               | 755nm                                                                               |
| Acne removal<br>Vascular treatment                                                | Freckles removal                                                                  | Skin rejuvenation<br>wrinkle removal                                              | Removal of visible blood vessels                                                  | Hair removal (fair skin)                                                           | Hair removal (medium skin tone)                                                     | Hair removal (darker skin)                                                          |

Standard configuration: 420nm 510nm 560nm 690nm

## Before and after



Skin rejuvenation



Freckle removal



wrinkle reduction



Acne clearance



Hair removal




Pigmentation treatment

1. 15.6 吋螢幕顯示  
 2. 6 吋螢幕顯示  
 3. OEM (原廠/組裝) 顯示...

## Suitable for any complexion

The elight handle is equipped with **seven filters**, which can be used for **different treatments** and **different skin colors** to select the corresponding filters, thus making the operation more convenient.



! 24 小時  
 隨時隨地