


360° bidirectional rotation

Rotating the machine without moving
Efficient and labor-saving



--... ..
!... .. *
... .. *
10-1 *hz.treatment !!!... ..

... ..!!




EVOLUTION OF HAIR REMOVAL


SAFE AND STABLE


3-5 SESSIONS TREATMENT

TO REMOVE HAIR PERMANENTLY



MORE





The handle can be placed **at will**



DO as one wishes

Exfu NEW ARRIVAL

Style: Stationary



1064 808 755 : 1064nm 808nm 755nm

755nm . 808nm . 1064nm

808nm . 1064nm

1064nm .

350g lightweight handle, more ergonomic

Available in black or white



spot size:12*36



spot size:12*24



spot size:12*36



spot size:12*24

Suitable for any unwanted hair on areas like face,arms,armpits,chest,back,bikini,legs...



EXFU

24*1.12 36*2.12mm



Authentication

FDA,NQA13485,CB certification
and more Complete certification
materials



60000+ Customers

We have professional after sale
team and we provide 7*24
services



2 Years Warranty

2 years warranty for each
machine, All questions will get
reponse within 24 hours

7 !!!!!!! 000 0000000 00X24 000000 00000 0000!