

Diode laser

hair removal machine

Safe • Fast • Painless • permanent



sdqym.en.alibaba.com

Frequency	Pulse	Energy	Total	Date
5	30	78	0	2023-05-08 11:25:11
5	30	78	0	2023-05-08 11:25:13
5	30	78	0	2023-05-08 11:25:17
5	30	78	0	2023-05-08 11:25:19

Multimedia Control System

Supports Bluetooth /Wifi /Remote control and locking/Cloud storage



* □□□□ □□□□□□ □□ □□□□ □□□□□□ □□ □□□□□□ □□□□ □□□□□□.

15.6" Smart Clinic Multimedia Monitor with HD 4K Screen



* 15.6" HD 4K Screen Resolution 3840x2160
 15.6" (395mm) Diagonal

* Android OS 5.0 (Lollipop) OS
 15.6" (395mm) Diagonal

15.6" (395mm) Diagonal

15.6" (395mm) Diagonal
 755 (nm808nm1064nm) 15.6" (395mm) Diagonal
 15.6" (395mm) Diagonal

36*12 / 24 * 12 ! (.
 .
 E).4K 16
 6 6
 16 .
 (OEM ODM / / /) ...

350g

Ultra light handle



12×36mm

Handle

1800W diode laser hair removal



12×24 mm

Handle

1200W diode laser hair removal

□□□□ □□□□ □□□□ □□

□□□□ □□ □□ .□□□□□□ □□□□□□ □□ □□□□ □ □□□□□ □□□□□□□□
 □□□□□□ □□ □□□□□□ □□□□□ □□□□ □□□□□□ □□□ □□□□□□
 □□□□ □□□□□ □□□□ □□□ □□□□ □□□□□

LASER COMPARISON

【Other - Lasers】



- ✓ The original structure is not light enough.
- ✓ Big dimension.
- ✓ Short life.

【2022-MLKJ-Lasers】



- ♥ Lighter weight.
- ♥ Smaller dimension.
- ♥ More advanced structure design.
- ♥ More advanced performance.

【2022-MLKJ-Medical-Lasers】



- ♣ More advanced packaging technology.
- ♣ Higher energy densit.
- ♣ Lighter appearance.
- ♣ Longer life.

What can
we do
in
1 MINUTE

Time for a cup of instant coffee,
the handle can quickly frost.





EXFU[®]
Simple · Safe · Enjoy



sdqym.en.alibaba.com

Suitable for hair removal on any part of the body,
Such as arms, legs, face, armpits, back, chest, etc.



□□□□ □□ □□□ □□□ □□□□ □□□□ □□□□ □□□□ □□□□.



IT'S TOO TO FAST

Easy to realize rental control,
Treatment data synchronization.

- Android OS
- Touch Screen
- Built-in Speaker

□□□□ □□ □□□□ □□ □□□□ □□□□!