

HIGH POWER DIODE LASER

755+808+1064nm
For all skin and hair types

Newest!

[Learn more details](#)

คุณสมบัติ

- .สามารถกำจัดขนได้ 16--8 ครั้งต่อขนแต่ละมัดจนขนไม่ขึ้นอีก *
- .สามารถกำจัดขนได้โดยไม่ต้องใช้ยา 3 วันขนจะขึ้นใหม่ 50 เปอร์เซ็นต์ *
- ขนขึ้นใหม่จะขึ้นช้าลงกว่าเดิม 1 ถึง 3 เท่าขึ้นอยู่กับ 755 นาโนเมตร 808 นาโนเมตร 1064 นาโนเมตร 3 *





Arm hair removal



Lip hair removal



Face hair removal



Leg hair removal



Back hair removal



Underarm hair removal



Bikini hair removal



DIODE LASER

755/808/1064nm diode laser, for all type skin hair removal, painless



ADVANTAGE

- **PAINLESS:** 755/808/1064nm diode laser for all type skin hair removal
- **FASTER:** Large area spot sliding operation
- **NO TRAUMA:** There is no trauma to skin tissue
- **SAFETY:** To avoid the light of the deputy to reduce the difficulty of operation



□□□□ □□□□□□

□□□□□□ □□□□□□ □□□□ □□ 1800 □□□□ 1200 □□□□ □□□□

□□□ □□□□ 35 * 12 □□ 20 * 12 □□□□ □□□□□□

350 *

*
0000



800/1000/1200/1600W
50 Million Shots
USA / Germany Imported Laser Bar

755nm+808nm+1064nm



ALEX 755nm
For white skin
(fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
(brown hair removal)



YAG 1064nm
For black skin
(black hair removal)




• *Cooling effect* •

The handle is frosted for one minute,
making your treatment more comfortable and painless



Suitable for hair removal on any part of the body,
Such as arms, legs, face, armpits, back, chest, etc.





-



111

□	□	□	□	□	□	□
---	---	---	---	---	---	---

□ □ □ □ □ □ □ □

□□□ □□□

□□ □□□

□□□□□

□□□□□□

□□□□□ □□□

1111

□□□□□

□ □ □ □ □ □ □

☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐

! 000000 0000 00 00 0000 0000 000000 000000 0000

□□□□ 24 □□□□□!!