



.பெரிய பருக்கி பெரிய பருக்கி

பெரிய பருக்கி பருக்கி பெரிய பருக்கி பெரிய பருக்கி *

பெரிய பருக்கி பருக்கி பெரிய பருக்கி *

பெரிய பருக்கி *


.பருக்கி பெரிய பருக்கி பெரிய பருக்கி பெரிய பருக்கி *

.பெரிய பருக்கி பெரிய பருக்கி *

10) பெரிய பருக்கி பெரிய பருக்கி *ms 800 (ms)

பெரிய பருக்கி **35*12** **20*15** பெரிய பருக்கி பெரிய பருக்கி பெரிய பருக்கி !பெரிய பருக்கி **350** பெரிய பருக்கி!

Handle display Handle color optional



weight **450g**

The handle weighs only 450g, making the treatment process easier

Cooling effect

Fast cooling, more comfortable treatment process



12*20mm



12*35mm



12*20mm




12*35mm

□□□□□ □□ □□□□□:

□□□ □□ □□□□□ □□□□□ □□□ □□□□□ Dual-TEC□

□□□□ □□□□ □□□□ □□□□ 24 □□□□ □□□ □□□ □□ □□□□□□ □□□ □□ □□□□□□□□□□.



The diagram illustrates a cross-section of a hair follicle. Key components and their associated laser parameters are labeled as follows:

- 755nm Alex**: Points to the **sebacous Gland**.
- 808nm Speed**: Points to the **Arrector Pili Muscic**.
- 1064nm YAG**: Points to the **Bulge**.
- 4mm**: A vertical bracket on the left indicates the length of the **Hair Bulb**.
- Follicular Papilla**: Points to the base of the hair bulb.






ALEX 755nm
For white skin
 (fine, golden hair removal)




SPEED 810nm
For yellow neutral skin
 (brown hair removal)



YAG 1064nm
For black skin
 (black hair removal)



Treatment Comparison





Smayer Laser

755/808/1064 nm Laser Diode Laser System for Hair Removal

3000 Watts

0-150J/cm² (Energy Density)

10-800ms (Pulse Width)

1-10 cm (Spot Size)

35*12 mm²/12*20mm²

12-10.4 inch TFT True Color LCD

TEC (Thermoelectric Cooling)

16 inch 12 inch 10 inch PCS

115*59*61 cm (Size)

OEM and **ODM**

. Smayer Laser is a professional manufacturer of laser equipment for hair removal.

. Smayer Laser has a professional R&D team and a complete production line.

. Smayer Laser has a professional sales team and a complete service network.

. Smayer Laser has a professional after-sales team and a complete service network.

. Smayer Laser has a professional R&D team and a complete production line.

. Smayer Laser has a professional sales team and a complete service network.

. Smayer Laser has a professional after-sales team and a complete service network.

. Smayer Laser has a professional R&D team and a complete production line.

Certificate display

Certificate is the best guarantee for you



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,