

Diode Laser



15 Bar **1800W** Handle

*Increase the treatment head of nasal hair
and treat small parts easily



.00000 0000 000000 0000 0000000
00000 000 00 0000 00000 00000000 0000 *

00000 000 00 0000 00000 *

0000 0 0000 *

.00 000 0000000 000 00000 0000000000 *

808 00000 0000 000 000 *nm 7558081064 00nm.

350g

Ultra light handle



12×36mm

Handle

1800W diode laser hair removal




12×24 mm

Handle

1200W diode laser hair removal

이 제품은 1064nm, 808nm, 755nm 세 가지 파장을 가진 레이저를 사용하여 모발을 파괴하는 데 사용됩니다. 1064nm는 깊은 모발을, 808nm는 중간 모발을, 755nm는 얇은 모발을 처리하는 데 적합합니다.

755nm (Alexandrite) 레이저는 표피층에 작용하여 모발을 파괴합니다.
808nm (Diode) 레이저는 모발의 중간층에 작용하여 모발을 파괴합니다.
1064nm (YAG) 레이저는 모발의 깊은 층에 작용하여 모발을 파괴합니다.
이 레이저는 모발의 생장 주기에 따라 주기적으로 사용해야 합니다.






ALEX 755nm
For white skin
 (fine, golden hair removal)




SPEED 810nm
For yellow neutral skin
 (brown hair removal)



YAG 1064nm
For black skin
 (black hair removal)



Treatment Comparison





Emergency
stop button

12 inch big screen
quick touch
easy operate

Diode laser handle

Vents

Plug