

Diode Laser



15 Bar **1800W** Handle

*Increase the treatment head of nasal hair
and treat small parts easily



.00000 0000 000000 0000 0000000
00000 000 00 00000 000000 00000000 00000 *
00000 000 00 00000 000000 *
00000 0 00000 *
.00 000 00000000 0000 0000000 00000000000 *
808 000000 00000 0000 0000 *nm 7558081064 00nm.

350g
Ultra light handle



12×36mm

Handle

1800W diode laser hair removal




12×24 mm

Handle

1200W diode laser hair removal

이 제품은 350g의 초경량 핸들, 1064nm YAG 레이저, 808nm Speed 레이저, 755nm Alex 레이저를 탑재하여 다양한 피부 타입에 적합합니다.

755nm (Alex 레이저)는 표피의 멜라닌 색소를 표적화하여 모낭을 파괴하고, 808nm (Speed 레이저)는 모낭의 멜라닌 색소를 표적화하여 모낭을 파괴하며, 1064nm (YAG 레이저)는 모낭의 멜라닌 색소를 표적화하여 모낭을 파괴합니다.






ALEX 755nm
For white skin
(fine, golden hair removal)




SPEED 810nm
For yellow neutral skin
(brown hair removal)



YAG 1064nm
For black skin
(black hair removal)



Treatment Comparison





Emergency stop button

12 inch big screen quick touch easy operate

Diode laser handle

Vents

Plug