

DIODE LASER HAIR REMOVAL MACHINE

00000 000000 00000 00 ICE MLKJ 000000 00 000000000 00000000 !00000 00000000000 000000000 00000 00
 0000000 .00000 0000000000 00 00000000 00000000 00 000 00000 00 0000 0 000 00000 0 000 00000 0 00000
 00000 00000 0000 0000000 0 000000 0000 00. !

15 Years Laser Beauty Device Manuafactor

• High Feedback
Top10 Supplier

• OEM & ODM
SERVICE



• *Cooling effect* •


The handle is frosted for one minute,
making your treatment more comfortable and painless



Suitable for hair removal on any part of the body,
Such as arms, legs, face, armpits, back, chest, etc.




- [illegible]



755 nm for white skin (fine, golden hair removal);




808 nm for yellow neutral skin (brown hair removal);



1064 nm for black skin (black hair removal)

1. 2. 3. 4. 5. 6.

1. 2. 3. 4. 5. 6.



■ 755nm (Alexandrite) レーザーは、メラニン色素をターゲットに、シミやそばかすを効果的に改善します。
■ 808nm (Diode) レーザーは、毛根をターゲットに、永久脱毛の効果が期待できます。
■ 1064nm (Nd:YAG) レーザーは、真皮層をターゲットに、たるみ改善や毛穴ケアに効果的です。

755nm (Alexandrite) レーザーは、メラニン色素をターゲットに、シミやそばかすを効果的に改善します。
808nm (Diode) レーザーは、毛根をターゲットに、永久脱毛の効果が期待できます。
1064nm (Nd:YAG) レーザーは、真皮層をターゲットに、たるみ改善や毛穴ケアに効果的です。

For all skin types

Triple wavelength laser work together

755
nm

808
nm

1064
nm

755nm/808nm/1064nm

755nm
808nm
1064nm

Laser hair removal treatment theory



Hair active growth phase(3-6years)



laser treatment



Transition phase (1-2weeks)



Resting phase (1-2 weeks)



Return to growth phase

□□□

808V29

□□□□ □□□

□□□□□□ □□□□□□□□ 755/808/1064 □□□ 3 □□ □□□□□□□□ 808 □□□□□ □□□□

□□□□ □□□□□

4 □□□□□ 14 □□□□□ □□□□K □□□ □□□□

□□□ □□□

755/808/1064

□□ □□□

20-40 □□□ □□□□□□□

□□□□□

10~150 j/cm2 □□□□□ □□□□

□□□□□□

1-10HZ

□□□□□ □□□

□□ □□□ □□□□□□□

□□□□

3500 □□□

□□□□ □□□□□□

12*24mm 36*12 □□mm □□□□□□ □□□□

□□□□□

110 □□□□□□ □□□□ □□□□ 50 / □□□ 220 □□ □□□□ 60 / □□□

□□□□ □□□

95 □□□□□□□

□□□□□□ □□□

105 □□□□□□□

□□□□□ □□□□□□

53*40*105 □□□ □□□□□

125*56*70.4

125*56*70.4



Painless 810nm-755nm
Diode laser handle
Suitable for all skin tones and body parts

125*56*70.4

125*56*70.4

125*56*70.4

125*56*70.4

125*56*70.4

125*56*70.4

Custom Section

LOGO design



SYSTEM design



1000000 1000

10000 1000000 1000 10000 10 10000 10 10 10000000 1000 10000 1000000 10 1000



Our customers

60000+ CUSTOMERS



102

Countries

OEM/ODM

Customize the machine according to customer needs

CERTIFICATE



14 我们拥有 102 个国家的客户，我们拥有 60000 多个客户！

13 我们拥有 102 个国家的客户，我们拥有 60000 多个客户！

我们拥有 102 个国家的客户，我们拥有 60000 多个客户！

我们拥有 102 个国家的客户，我们拥有 60000 多个客户！

我们拥有 102 个国家的客户，我们拥有 60000 多个客户！

我们拥有 102 个国家的客户，我们拥有 60000 多个客户！

我们拥有 102 个国家的客户，我们拥有 60000 多个客户！

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service,