




00000 0000000



0000 00000






Laser show Handle laser bar optional



④ 10bar

④ 12bar

④ 16bar



□□□□ □□□□□□ □□ □□ □□□□

Suits for all skin and hair types



808nm

1064nm



- **755nm for white skin** (fine, golden hair removal)

● **808nm for yellow neutral skin** (brown hair removal)

- **1064nm for black skin** (black hair removal)




- 1.** _____ **15** _____.

2-□□□ □□□ □□□□ □□□ □ □□□□ □□□ □□ □□□□□ □□□□ □□□□ □□□□□.

3. 本公司 2023 年 TEC 项目 在 前 三 季 度 内 完 成 的 项 目 数 量 较 上 年 同 期 增 加 了 100 个。

Treatment Comparison



□□□□ OEM

1. □□□□□ □□□ □ □□□
2. □□□□□□□ □□□□ □□□□□ □□ □□□□□ □□□ □□□□

customer visit



Packing

Safe and thoughtful packaging service



Tight packaging

The machine shall be made of waterproof materials and packaged

**Anti collision foam board
inside aluminum box**



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service