



DIODE LASER HAIR REMOVAL MACHINE

- SUPER ICE PAINLESS EXPERIENCE
- PERMANENT HAIR REMOVAL
- COMFORTABLE HAIR REMOVAL

1min} Fast and painless hair removal
One minute cooling -21°C



Large Spot Size

Quick and Comfortable

With large spot size of 1.2*3.5cm², for faster treatments and better patient experience.



TEC Plus

Continuous Contact Cooling

TEC is an advanced technology that continuously cools skin and facilitates range-controlled temperature throughout the entire treatment. Patients can now enjoy a completely pain-free, cool and comfortable experience throughout the session.

□□□□□

*□□□□□ 40 □□ □□ □□□□□□ □□□□ □□□□ □□□

□□□□ □□□□ □□ □□□ 1600 □□□□ 16 □ □□□ 1200 □□□□ 12 □□□□ 1000 □□□□ 10 □□□□ □□□□□*

□□□□□ □□□□ □□□□ □□□□ 38 * 12 □□□□ □□□□ 25 * 15 □□□□ □□□□ 20 * 12 □□□□ □□□□□□ *

□□□□□□ □□□□□□ □□□□ □□□□ □□□□ □□□□ 450 □□□□ *

□□□□ □□□□□□□ □□□□ □□□□ □□ □(□□□□ □ □□□□□□ □□□□) □□□ □□□□□ □□□□ □□□□ □□□□□□□□ □□□□ □□ *

Handle Details


Three Wavelengths Work Togher





12*20nm


755nm Laser
808nm Laser
1064nm Laser





12*35nm

755nm Laser
808nm Laser
1064nm Laser



□□□□ □□□□□ □□□□ □□ □□□□ □□□□□□□□

□□□□ □□□□ □□□□ □□□□□□□□ 755 □□□□


Speed Diode 808nm □□□□ □□□□ □□□□

Long Pulse 1064nm □□ □□□□ □□□ □□□□ □□□□

Working Principle

Triple wavelength laser work together

Suits for all skin and hair types



- **755nm for white skin** (fine, golden hair removal)
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)

□□□□□□ □□



□□□□ □□□□

1. □□□□ □□ □□□□□□ 12.4 □□□□ □□□□□ □□□□
- □□□ 6 □□□□ □□□□ 6 □□□□ □ □□□ □□□□□ □□□□□ □□□□ □□□□ .2
- □□□□□ □□□□ □□ □□□ □□□□□ □□□□ □□□□□ □□□□□ 6 .3
- □□□□□□ □□□□□□ .4 OEM (□□□□□□/□□□□□□...)