



IPL A6
 For hair removal
 & skin rejuvenation

1. 8.4 inch LCD true color touch screen
 2. IPL handle
 3. Emergency Switch
 4. Key Switch
 5. 30000-150000 pulses
 6. 50 * 15 cm treatment area
 7. 8.4 inch TFT LCD screen
 8. 30000-150000 pulses
 9. 50 * 15 cm treatment area
 10. 8.4 inch TFT LCD screen



8.4 inch LCD true color touch screen

Elight Handle Design



Specification

Optional Spot Size:
15*50mm

Imported UK lamp

Long shots time:
150,000--300,000 times

7filters:
420/510/560/585/640/690/755nm

Super cooling system



□□□□ □□□□□□ □□ □□□□□□ □□□□□ □□□□□ □□□□□ □□□□ □□□□□.



□□□□□ **8.4** □□□□□ □□□□ □□□□ □□□□ □□□□□□□□□□
1. □□□□□□ □□□□□□ □□□□□□□□ 8.4 □□□□□ □□□□□ □□□□□

- .2 6 2
- .3
- .4 OEM ()

Screen interfac

Professional Screen, Easy operation



Main Menu
8.4 inch true color big touch screen
Super cool touch Experience.



IPL mode:
5 options for skin treatment




IPL mode:
operation interface



Multi-language screen:
6 languages for your choice



System setting



System setting

1. 6 languages
 2. 8.4 inch
 3. 150000-30000
 4. 8.4 inch
 5. TEC 1200W 1 3
 6. 2
 7. AU 110 220
 8. 30
 9. 110V/220V
 10. 110V/220V

IPL: 50 * 15
 420/510/560/585/640/690/755nm
 150000-30000
 8.4
 TEC 1200W 1 3
 2
 AU 110 220
 30
 110V/220V
 110V/220V

Multi-angle display



Left view



Front view



right elevation