

The image is a promotional graphic for diode laser hair removal. On the left, a woman's legs are shown from the knees down, with her hands resting on her thighs. On the right is a black, professional-grade laser machine with a control panel featuring a screen and various buttons. A stylized, wavy white line connects the machine to the woman's legs, suggesting the laser's path. The background is a clean, light gray.

DIODE LASER HAIR REMOVAL

PAINLESS HAIR REMOVAL, NO SIDE EFFECT

MORE

Sync to machine

SMART CLING

Intelligent | Interconnected | Efficient



1. $\frac{\text{တစ်ခုခု} / \text{တစ်ခုခု တစ်ခုခု တစ်ခုခု} / \text{တစ်ခု နှင့် တစ်ခု တစ်ခု တစ်ခု တစ်ခုခု} / \text{တစ်ခု တစ်ခု တစ်ခုခု} / \text{တစ်ခုခုခု တစ်ခု တစ်ခုခုခုခုခု}$
 တစ်ခု တစ်ခု တစ်ခု
 $\text{တစ်ခုခုခု တစ်ခု တစ်ခု} .2$
- $\text{တစ်ခုခု တစ်ခုခု တစ်ခုခု တစ်ခုခု တစ်ခုခု} .3$
- $\text{တစ်ခု တစ်ခုခု} .\text{တစ်ခု တစ်ခုခု တစ်ခု တစ်ခု တစ်ခု တစ်ခု တစ်ခုခုခုခုခု} .4$
- $\text{တစ်ခု တစ်ခုခု တစ်ခုခု တစ်ခု တစ်ခုခုခု တစ်ခု တစ်ခုခုခု} .5$

Frequency	Pulse	Energy	Total	Date
5	30	78	0	2023-05-08 11:25:11
5	30	78	0	2023-05-08 11:25:13
5	30	78	0	2023-05-08 11:25:17
5	30	78	0	2023-05-08 11:25:19

Multimedia Control System

Supports Bluetooth /Wifi /Remote control and locking/Cloud storage



* 本系统支持蓝牙/WiFi/远程控制/锁定/云存储。

15.6" Smart Clinic Multimedia Monitor with HD 4K Screen



* 15.6" Smart Clinic Multimedia Monitor with HD 4K Screen
15.6" Smart Clinic Multimedia Monitor with HD 4K Screen

* 15.6" Smart Clinic Multimedia Monitor with HD 4K Screen
15.6" Smart Clinic Multimedia Monitor with HD 4K Screen

15.6" Smart Clinic Multimedia Monitor with HD 4K Screen

15.6" Smart Clinic Multimedia Monitor with HD 4K Screen
755 (nm808nm1064nm) 15.6" Smart Clinic Multimedia Monitor with HD 4K Screen
15.6" Smart Clinic Multimedia Monitor with HD 4K Screen

350g
Ultra light handle

12×36mm
Handle
1200W diode laser hair removal

12×24 mm
Handle
1200W diode laser hair removal

0000 000 00 .0000000 0000000 000 0000 0 000000 0000000000
 0000000 000 000000 000000 0000 0000 0000000 000 000 000000
 00000 000000 000000 000 00000 00000 000000

LASER COMPARISON

【Other - Lasers】



- ✓ The original structure is not light enough.
- ✓ Big dimension.
- ✓ Short life.

【2022-MLKJ-Lasers】



- ♥ Lighter weight.
- ♥ Smaller dimension.
- ♥ More advanced structure design.
- ♥ More advanced performance.

【2022-MLKJ-Medical-Lasers】



- ♣ More advanced packaging technology.
- ♣ Higher energy densit.
- ♣ Lighter appearance.
- ♣ Longer life.

What can
we do
in
1 MINUTE

Time for a cup of instant coffee,
the handle can quickly frost.




EXFU[®]
Simple · Safe · Enjoy



sdqym.en.alibaba.com

Suitable for hair removal on any part of the body,
Such as arms, legs, face, armpits, back, chest, etc.



□□□□□ □□□ □□□□ □□□□ □□□□ □□□□ □□□□ □□□□.



IT'S TOO TO FAST

Easy to realize rental control,
Treatment data synchronization.



Android OS



Touch Screen



Built-in Speaker

□□□□□ □□□ □□□□□□ □□ □□□□□□ □□□□□□!