



D10

Portable Hair Removal Machine

Three bands: 755nm/808nm/1064nm  
Suitable for all skin types

DIODE LASER hair removal machine

■ 2 Years Warranty ■ OEM / ODM Service ■ 3 waves 1064nm + 808nm + 755nm



DIODE LASER hair removal machine D10

- \* 12--8 1064nm 808nm 755nm 1064nm 808nm 755nm.
- \* 3 1064nm 808nm 755nm 50 1064nm 808nm 755nm.
- \* 3 1064nm 808nm 755nm 1 1064nm 808nm 755nm 1064nm 808nm 755nm

# Handle Display

Two colors, two spot sizes are optional



1064nm 808nm 755nm : 1064nm 808nm 755nm

755nm 808nm 1064nm 1064nm 808nm 755nm

808nm 1064nm 808nm 1064nm 808nm

1064nm 808nm 1064nm 808nm 1064nm

# *Working Principle*

755nm and 808nm and 1064nm , suits for all skin and hair types.



**ALEX 755nm**

**For white skin**

(fine, golden hair removal )



**SPEED 810nm**

**For yellow neutral skin**

(brown hair removal)



**YAG 1064nm**

**For black skin**

(black hair removal)



# The real experience is visible

Through live test verification ,safe ,long,painless  
and effective



- 1) .000 00 0000000 00000 14 0000 0000 00000 0000 :0000 0000000  
.000 0000 0000 00000 00000 00000 000 00 :0000000 0000 (2  
00000 (3 OEM: 00 000 000 00000 0000 000000 000000 00000 00 00000 0000 00 0000 00 00 0000 0000  
0000000.



# Product details

Ultra-thin large screen, cool light strip



!0000 00000 00 00 0000 0000000 000000 00000  
000000 0000 24!