

12*24mm or 12*36mm handle

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...



1800W 1200W 36*12 24*12 * 350

* TEC (Thermoelectric Cooling) system

One minute cooling -27°C

Best TEC Cooling system hair remover laser

* TEC (Thermoelectric Cooling) system

* 100% 100% 100% 100% 100% 100%
 * 100% 100% 100% 100% 100%
 100% 100%

Hair removal comparison

The real picture taken by the customer

Different parts of men and women, as well as different skin colors can have very good hair removal results, they all get a permanent and painless hair removal experience



Before



After Treatment

Hair removal comparison

The real picture taken by the customer

Different parts of men and women, as well as different skin colors can have very good hair removal results, they all get a permanent and painless hair removal experience



Before



After Treatment

100% 100%

100% 100% 14 100% 100% 100% .1

100% 100% 6 100% 100% 6 100% 100% 100% 100% 100% 100% .2

100% 100% 100% 100% 100% 100% 100% 100% 6 .3

100% 100% 100% .4 OEM (100%/100%...)

5. 100% OEM / ODM

>>OEM your own machine body

>>OEM your own program software

>>OEM pretty machine colors

>>Print your LOGO on machine body and screen

>>R & D team and Quality inspection Show

6. 000000 000000

0000 000000 00.0000000000 000000 00 .000000 0 000000 00000000 00 000000 0 000000 0000 0000 000000 0 000000 000000
00 00000000 00 0000 0000 0000 00 000000 00 00 000000 00 000000 .000000 00000000 0000 0 0000 00000000 0 0000 000000
000000 00000000 0000 000000000000 000000 000000.

000000 000000000000

- 0000 808V19
- 0000 0000 0000 18 000000 12 000000000 0000000/000000
- 0000 000000 4 000000 14 000000 0000K 0000 00000
- 0000 0000 808mm 755 00mm 808mm 1064mm
- 00 0000 20-40 0000 00000000
- 000000 10~150 j/cm2 000000 00000
- 00000000 1-10 00000
- 000000 0000 000000 0000 00 TEC 000000 00000 00000 00000 00000 0000 0000 00 00000 00 00000 0 0000 000000 00000 00
- 00000 3500 0000
- 00000 00000000 12*24mm 36*12 00mm 00000000 00000
- 000000 110 0000000 00000 00000 50 / 0000 220 00 00000 60 / 0000
- 00000 0000 95 00000000
- 0000000 0000 105 00000000
- 000000 00000000 53*40*105 0000 0000000
- 00000 00000000 125*56*70.4

000000 000000 000000

- 000000 000000 3-7 00000000 00 00 000000 0000
- 000000 0000 0000 000000 0000 DHL TNT Fedex 0000000 0000000000 00
- 0000000 00 0000 00000000 0 000000 0000
- 0000000 00 00 0000 0 0000 00 000000 0000000 00000 0000 2 :000000000
- 000000 000000 00 0000 0 0000000 00 0000 00 0000000000000 00000

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

