



From Israel Technology

FOR ALL SKIN TYPE HAIR REMOVAL

- 100% Ice Cooling
- 100% Permanent
- 100% Painless

. ׁׁׁׁׁ ׁׁׁׁ ׁׁׁׁ ׁׁׁׁ ׁׁׁׁׁׁׁׁ
 ׁׁׁׁׁ ׁׁׁ ׁׁ ׁׁׁׁ ׁׁׁׁׁׁׁׁ ׁׁׁׁׁׁׁ *
 ׁׁׁׁׁ ׁׁׁ ׁׁ ׁׁׁׁ ׁׁׁׁׁׁׁ *
 ׁׁׁׁׁ ׁ ׁׁׁׁ *
 .ׁׁׁ ׁׁׁׁׁׁׁׁ ׁׁׁ ׁׁׁׁׁׁׁׁׁׁׁ *
 ׁׁׁׁׁׁׁׁ 1064 808 755 ׁׁ ׁׁׁׁׁׁׁׁ 808 ׁׁׁׁׁׁׁׁׁ ׁׁׁׁ ׁׁׁׁ *.

350g
 Ultra light handle



12x36mm

Handle

1800W diode laser hair removal



12x24 mm

Handle

1200W diode laser hair removal

□ □□□ □□□□ □□□□ □□ □□ □□□□□□ **1064** □□□□□□ **808** □□□□□□ **755** □□ □□□□□□ □□□ □□ □□□□ □□□□ □□.

755 .(□□□□□/□□□□□ □□□□□) □□□□ □□□□ □□□□ □□□□ □□□□ □□□□□□□□
808nm .(□□□□□□) □□□□ □□□□ □□□□ □□□□ □□□□ □□□□
□□□□ □□□□□) □□□□ □□□□ □□□□ □□□□ □□□□ □□□□ □□□□□□□□ 1064).




ALEX 755nm
For white skin
(fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
(brown hair removal)



YAG 1064nm
For black skin
(black hair removal)



Treatment Comparison

