



24 ชั่วโมง บริการทุกวัน!!!
.บริการทุกวัน 24 ชั่วโมง บริการทุกวัน!!!

350g lightweight **handle**, more ergonomic

Available in **black or white**



1064 808 755 □□□□ □□□□ □□□□ □□□□ □□□□ □□□□□□

□□□ 1000 □□□□ 10 □□□□ □□□□ 20 * 12 □□□□ □□□□□□.

.000 1200 0000 12 0000 0000 35 * 12 0000 000000
 000 1600 0000 16 0000 0000 35 * 12 0000 000000.

□□□□ □□□□□□ □□□ □□□□□□ □□□□

□□ □□ □□□ □□□ □□□□ □□□ □□ □□ □□□ □□□ □□□□ □□ □□



1064 808 755 www.facebook.com/essku www.instagram.com/essku www.youtube.com/channel/UCv33333333333333333333

1) www.facebook.com/essku www.instagram.com/essku www.youtube.com/channel/UCv33333333333333333333



2) www.facebook.com/essku www.instagram.com/essku www.youtube.com/channel/UCv33333333333333333333

www.facebook.com/essku www.instagram.com/essku www.youtube.com/channel/UCv33333333333333333333 (3.




0000 0000 0000 0 0000 00 0000 00 0000 00 0000





The new **14-inch 4K** screen

Support system customization



产品特点 产品特点

波长	755 nm 808nm 1064nm
脉冲宽度	16 --- 8000000 脉冲
脉冲间隔	100 毫秒
脉冲频率	0.5-10 Hz 可调
光斑大小	12 * 35 mm 20 * 12 / 25 * 12 mm
能量范围	808 nm 40000000-100000000 J/cm2
能量密度	10-150 J / cm2 150 J/cm2 可调
冷却系统	TEC 冷却系统
功率	800w/1000w/1200w/1600w
重量	2000 克
尺寸	220 * 110 * 50 mm
电压	AC220V/110V 50~60Hz

产品特点 产品特点 产品特点 产品特点 产品特点 产品特点!