



From Israel Technology

FOR ALL SKIN TYPE HAIR REMOVAL

- 100% Ice Cooling
- 100% Permanent
- 100% Painless

. ׁׁׁׁׁ ׁׁׁׁ ׁׁׁׁׁ ׁׁׁׁ ׁׁׁׁׁׁׁ
 ׁׁׁׁׁ ׁׁׁ ׁׁ ׁׁׁׁ ׁׁׁׁׁ ׁׁׁׁׁׁׁ ׁׁׁׁ *
 ׁׁׁׁׁ ׁׁׁ ׁׁ ׁׁׁׁ ׁׁׁׁׁ *
 ׁׁׁׁׁ ׁ ׁׁׁׁ *
 .ׁׁׁ ׁׁׁׁ ׁׁׁׁׁׁׁ ׁׁׁ ׁׁׁׁׁׁׁׁׁ *
 ׁׁׁׁׁׁׁ 1064 808 755 ׁׁ ׁׁׁׁׁׁׁׁ 808 ׁׁׁׁׁׁ ׁׁׁׁ ׁׁׁ ׁׁׁ *.

350g
 Ultra light handle




12x24 mm
Handle
 1200W diode laser hair removal



12x36mm
Handle
 1800W diode laser hair removal

ׁ ׁׁׁׁ ׁׁׁׁׁ ׁׁׁׁ ׁׁ ׁׁׁׁׁׁׁ 1064 ׁׁׁׁׁׁׁ 808 ׁׁׁׁׁׁׁ 755 ׁׁ ׁׁׁׁׁׁׁׁׁ ׁׁׁ ׁׁ ׁׁׁׁׁׁׁׁ ׁׁׁׁׁׁׁׁׁ.

755nm .(Alex) 808nm .(Speed) 1064nm .(YAG)




ALEX 755nm
For white skin
 (fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
 (brown hair removal)



YAG 1064nm
For black skin
 (black hair removal)



Treatment Comparison

