

Medical handle is Lighter handle

Stronger, Faster, Smarter

1600w big handle power 24 hours working Painless hair removal



● 12*24mm²



● 12*36mm²

[Learn more](#)



14 102 2

14 60000 102 2

MLKJ— 102 2

Machine advantage:

- Machine warranty 2 years
- Custom language system
- 1800w high power hair removal
- Fast and safe



The image shows a professional-grade laser hair removal machine. It is a black, upright unit with a tablet screen at the top displaying two handpiece options. The machine has a control panel with a yellow emergency stop button, a power switch, and indicator lights. It is equipped with two handpieces: a large one for full-body treatments and a smaller one for facial treatments. The machine is mounted on four casters for mobility.

- ## Machine advantage:
- Machine warranty 2 years
 - Custom language system
 - 1800w high power hair removal
 - Fast and safe
- 
- The image shows a professional-grade laser hair removal machine. It is a black, upright unit with a tablet screen at the top displaying two handpiece options. Two handpieces are attached to the top: one is black and the other is yellow. The machine has a control panel with a yellow emergency stop button, a power switch, and several indicator lights. It is mounted on four casters for mobility. The background is a simple grey and white geometric design.



00000000
 0000 00000000 00000 00000 0000 0000 00000 1 00 3 0000000000 755 000000000 808 00000 000000000 1064 0000 1.3
 00 0000000 00000 0000 1800 / 0000 1200 00000 00000 :00000 00000
 !0000 0 00000 00 000000000 36*12 0000000000 24*12 00000000 00 0000 000000 00000 00000 000000 .2
 0000 00 0000000 00000000 0000 0000000 :0000000 0000 0000000 .3 Dual-TEC 00000000 0000 00 0000000000 00000 0000000000
 .00000 00000 00000 00000 24 00000 0000 00000 00
 0000000 0000000 00 000000000000 0000000 :0000 0000.4

00000000
 0000 00000000 00000 00000 0000 0000 00000 1 00 3 0000000000 755 000000000 808 00000 000000000 1064 0000 1.3
 00 0000000 00000 0000 1800 / 0000 1200 00000 00000 :00000 00000
 !0000 0 00000 00 000000000 36*12 0000000000 24*12 00000000 00 0000 000000 00000 00000 000000 .2
 0000 00 0000000 0000000 0000 0000000 :0000000 0000 0000000 .3 Dual-TEC 00000000 0000 00 0000000000 00000 0000000000
 .00000 00000 00000 00000 24 00000 0000 00000 00
 0000000 0000000 00 00000000000 0000000 :0000 0000.4

00000000
 0000 00000000 00000 00000 0000 0000 00000 1 00 3 0000000000 755 000000000 808 00000 000000000 1064 0000 1.3
 00 0000000 00000 0000 1800 / 0000 1200 00000 00000 :00000 00000
 !0000 0 00000 00 000000000 36*12 0000000000 24*12 00000000 00 0000 000000 00000 00000 000000 .2
 0000 00 0000000 0000000 0000 0000000 :0000000 0000 0000000 .3 Dual-TEC 00000000 0000 00 0000000000 00000 0000000000
 .00000 00000 00000 00000 24 00000 0000 00000 00
 0000000 0000000 00 00000000000 0000000 :0000 0000.4

00000000
 0000 00000000 00000 00000 0000 0000 00000 1 00 3 0000000000 755 000000000 808 00000 000000000 1064 0000 1.3
 00 0000000 00000 0000 1800 / 0000 1200 00000 00000 :00000 00000
 !0000 0 00000 00 000000000 36*12 0000000000 24*12 00000000 00 0000 000000 00000 00000 000000 .2
 0000 00 0000000 0000000 0000 0000000 :0000000 0000 0000000 .3 Dual-TEC 00000000 0000 00 0000000000 00000 0000000000
 .00000 00000 00000 00000 24 00000 0000 00000 00
 0000000 0000000 00 00000000000 0000000 :0000 0000.4

00000000
 0000 00000000 00000 00000 0000 0000 00000 1 00 3 0000000000 755 000000000 808 00000 000000000 1064 0000 1.3
 00 0000000 00000 0000 1800 / 0000 1200 00000 00000 :00000 00000
 !0000 0 00000 00 000000000 36*12 0000000000 24*12 00000000 00 0000 000000 00000 00000 000000 .2
 0000 00 0000000 0000000 0000 0000000 :0000000 0000 0000000 .3 Dual-TEC 00000000 0000 00 0000000000 00000 0000000000
 .00000 00000 00000 00000 24 00000 0000 00000 00
 0000000 0000000 00 00000000000 0000000 :0000 0000.4

TEC cooling system

One minute cooling -21°C

Best **TEC Cooling** system
hair remover laser



Hair removal principle

Make Your Beauty Business More Easier





The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area

Natural hair loss, prevent regeneration, and achieve the purpose of hair removal

Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth





755 nm for white skin (fine, golden hair removal);

808 nm for yellow neutral skin (brown hair removal);

© 2005 Blackwell Publishing Ltd

1064 nm for black skin (black hair removal)

□□□□ □□□□□□ □□ □□□□ □□□□□□ **40-20** □□□□□□ □□□ □□□

□□ □□ □□□ □□□ □□ □□□□ □□□ □□ □□□ □□□□ □□ □□□ □□□□

□□□□ □□□ 755/808/1064 □□□ 3 □□ □□□□□□□□ 808 □□□□□ □□□□

□□□□ □□□□ □□□□ 14 □□□□ □□□□ □□□□ □□□□

808 755/808/1064

□□ □□□ 40 □□□ □□□□□□

照射量 10~150 j/cm² 照射時間 照射量

□□□□□□ 1-10 □□□□


Certificate display

Certificate is the best guarantee for you



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

□□□□ □□□□

1. □□□□ Weifang Mingliang □□□ □□□□□□ □□□□□□ □□□□ □□ □□□□ □□□ 14 □□□□□

Customer visit



2. 醫務人員 與 顧客 醫務人員 醫務人員 醫 醫務人員 醫務 醫

3. 醫務人員 醫務人員 醫 醫務人員 醫務人員 醫 醫務人員 OEM 醫務人員 醫務人員 OEM 醫 醫務 醫務 醫務人員 醫 醫務人員 醫務人員....