

12*24mm or 12*36mm handle

Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...




3. 1200W 12*24mm 1200W 12*24mm 1200W 12*24mm

1. Alex 755nm 1200W 12*24mm 1200W 12*24mm

2. 1200W 12*24mm 1200W 12*24mm 808 1200W 12*24mm

3. 1200W 12*24mm 1200W 12*24mm 1064 1200W 12*24mm



Hair removal comparison

The real picture taken by the customer
 Different parts of men and women, as well as different skin colors can have very good hair removal results, they all get a permanent and painless hair removal experience



Before



After Treatment

Hair removal comparison

The real picture taken by the customer

Different parts of men and women, as well as different skin colors can have very good hair removal results, they all get a permanent and painless hair removal experience



Before



After Treatment

4. OEM / ODM

14 OEM (OEM/ODM...)

6 OEM (OEM/ODM...)

6 OEM (OEM/ODM...)

4 OEM (OEM/ODM...)

5. OEM / ODM

>>OEM your own machine body

>>OEM your own program software

>>OEM pretty machine colors

>>Print your LOGO on machine body and screen

>>R & D team and Quality inspection Show

6. OEM / ODM

Build more trusted partners

Our customers

60000+ CUSTOMERS


OEM/ODM

Customize the machine according to customer needs



CERTIFICATE

Obtained multi-way authoritative certification, product testing certification, product patent authority,



7. 如何 如何 如何

如何 如何 3-7 如何 如何 如何 如何
 如何 如何 如何 DHL TNT Fedex 如何 如何 如何 如何
 如何 如何 如何 如何 如何 如何
 如何 如何 如何 如何 如何 如何 如何 2 :如何 如何
 如何 如何 如何 如何 如何 如何 如何 如何

!如何 如何 如何 如何 如何 如何 如何 如何
 如何 如何 如何 24!!