

## **2in1 multifunctional combined hair removal machine**

*Hair removal and skin rejuvenation  
One machine double effect*



**808+Elight**

□□□□□□ □□□□□□




Elight handle

[illegible]


\* Elight 30,000-150,000 pixels per inch resolution, 1064 pixels, 808 pixels, 755 : pixels per inch \*

## *Three wavelengths work together*

**12\*24mm<sup>2</sup>** {




**12\*35mm<sup>2</sup>** {



Suitable for hair removal on any part of the body,  
Such as arms, legs, face, armpits, back, chest, etc.







## ELIGHT HANDLE

### specification

- High-quality: Elight handpiece with super cooling system
- Optional Spot Size 15\*50mm, 15\*35mm
- Long shots time: 150000 times
- 7 filters: 420/510/560/585/640/690/755nm  
Standard: 420/510/680nm



## Before and after



Skin rejuvenation



Freckle removal



wrinkle reduction



Acne clearance



Hair removal



Pigmentation treatment

## Hair removal and skin rejuvenation one machine and two effects

*2in1 Multifunction*



### 808 handle

Painless hair removal, Permanent hair removal, Suitable for all skin tones.




### Elight handle

Elight for hair removal, skin rejuvenation, vascular therapy, pigmentation therapy, acne therapy.

# 7-ADVANTAGE

## • Counter

The handle is equipped with an energy counter to clearly understand the total count during use.



## • German imported laser

808 handle adopts Germany imported laser, which has stronger energy and long service life.

## • Big spot size

808 handle uses large light spot of 12×35 mm, with large processing area and higher working efficiency. The Elight handle uses a 15×50 mm large light spot.



## • Cooling Effect

The handle adopts refrigeration effect, which can effectively cool the skin in the treatment process and improve the comfort of treatment.

## • Elight lamp

The e light handle uses IPL lamps imported from the United Kingdom, which emit light up to 150,000 times and have a longer service life.




## • Rf function

The e light handle is added with RF function, and the RF function after depilation can achieve the effect of tightening and lifting.

## • Optical filter

The e light handle is equipped with seven filters, which can be used for different treatments and different skin colors to select the corresponding filters, thus making the operation more convenient.






# 14inch true touch screen

6 kinds skin type for choice. accept ODM OEM Service.

The new **14-inch** screen is clear easy to operate.



歡迎參觀 歡迎選購 歡迎諮詢 歡迎合作 歡迎代理 歡迎經銷 歡迎批發 歡迎零售 歡迎批發 歡迎零售

歡迎批發 24 小時服務!!