



DIODE LASER HAIR REMOVAL MACHINE

LEARN MORE

[illegible][illegible]


* 10-1 .treatment . . . !!!



755 nm for white skin (fine, golden hair removal);



808 nm for yellow neutral skin (brown hair removal);



1064 nm for black skin (black hair removal)

0000 0000000

1. 00000 000 000 00 00000 0000000 00 00000 000000 0000 00000000 .2 .000 000 00 0000 00000
0000 00 00 0 0000 00000 00000 000000 000 00000 .4 00000 00000 00000 000000 000000 .3 .40,000,000
00000 000 6 00 000000 5.14.0 000000 000 00000 0000000.

Handle Details

Three Wavelengths Work Togher



□ □□□□ □□□□□ □□□□ □ □□□□ □□□□ □□ □□□□□□ **1064** □□□□□□□ **808** □□□□□□□ **755** □□□□□ □□□□ □□□ □□□□□ □□.

755 .(□□□□□/□□□□□ □□□□□) □□□□ □□□□ □□□□ □□□□ □□□ □□□□□□□□
808nm .(□□□□□□) □□□ □□□□ □□□□ □□□□□ □□□ □□□□
□□□□ □□□□□) □□□□ □□□□ □□□□ □□□□ □□□ □□□□ □□□□□□□□ 1064).

For all skin types

Triple wavelength laser work together

755
nm

808
nm

1064
nm

755nm/808nm/1064nm

755nm
808nm
1064nm

Laser hair removal treatment theory



Hair active growth
phase(3-6years)



laser treatment



Transition phase
(1-2weeks)



Resting phase
(1-2 weeks)



Return to growth
phase

□□□□ □□□□□□□□







型號	808V29
適用部位	面部、頸部、胸部、腹部、四肢、全身
適用人群	18-60 歲男女老幼
適用皮膚	755/808/1064 nm 三種波長
適用溫度	20-40℃
適用時間	10~150 j/cm ²
適用頻率	1-10HZ
適用功率	3500 W
適用面積	12*24mm 36*12 mm
適用次數	110 次/分鐘
適用時間	50 / 220 分鐘
適用溫度	95℃
適用功率	105 W

□□□□ □□□□□□ 125*56*70.4

□ □ □ □ □ □ □ □

- ```
* 14.0 0000
* 00 0000
* 00000 00000 000000 000 00000 00000 00 0000 000000
* 000 0000 00 00 000000 0000 0 000 scr 000 000000
```



☐ ☐ ☐ ☐    ☐ ☐ ☐ ☐ ☐ ☐    ☐ ☐    ☐ ☐    ☐ ☐ ☐

# Our customers

60000+ CUSTOMERS



102

Countries

OEM/ODM

Customize the machine according to customer needs

CERTIFICATE



14 我们拥有 102 个国家 60000+ 客户 102 个国家 60000+ 客户!

13 我们拥有 102 个国家 60000+ 客户 102 个国家 60000+ 客户!

我们拥有 102 个国家 60000+ 客户 102 个国家 60000+ 客户!

我们拥有 102 个国家 60000+ 客户 102 个国家 60000+ 客户!

我们拥有 102 个国家 60000+ 客户 102 个国家 60000+ 客户!

我们拥有 102 个国家 60000+ 客户 102 个国家 60000+ 客户!

我们拥有 102 个国家 60000+ 客户 102 个国家 60000+ 客户!

# PACKING

Safe and thoughtful packaging service



Built-in prevention  
collision bubble

Two- year warranty for machine  
handle as consumable,  
one-year warranty

Tight packaging

Training:  
(video +manual+online service)  
can keep you operate it easily



3-5 business days  
delivery

professional guide:  
24 hours professional online  
customer service