



1. CE ISO13485 2. 3. 4. 5. 6. 7. 8. 9. 10. 11. 12. 13. 14. 15. 16. 17. 18. 19. 20. 21. 22. 23. 24. 25. 26. 27. 28. 29. 30. 31. 32. 33. 34. 35. 36. 37. 38. 39. 40. 41. 42. 43. 44. 45. 46. 47. 48. 49. 50. 51. 52. 53. 54. 55. 56. 57. 58. 59. 60. 61. 62. 63. 64. 65. 66. 67. 68. 69. 70. 71. 72. 73. 74. 75. 76. 77. 78. 79. 80. 81. 82. 83. 84. 85. 86. 87. 88. 89. 90. 91. 92. 93. 94. 95. 96. 97. 98. 99. 100.



1. 2. 3. 4. 5. 6. 7. 8. 9. 10. 11. 12. 13. 14. 15. 16. 17. 18. 19. 20. 21. 22. 23. 24. 25. 26. 27. 28. 29. 30. 31. 32. 33. 34. 35. 36. 37. 38. 39. 40. 41. 42. 43. 44. 45. 46. 47. 48. 49. 50. 51. 52. 53. 54. 55. 56. 57. 58. 59. 60. 61. 62. 63. 64. 65. 66. 67. 68. 69. 70. 71. 72. 73. 74. 75. 76. 77. 78. 79. 80. 81. 82. 83. 84. 85. 86. 87. 88. 89. 90. 91. 92. 93. 94. 95. 96. 97. 98. 99. 100.

One minute cooling -27°C


Best **TEC Cooling** system
hair remover laser

A hand wearing a white glove holds a black laser hair removal device with a white cooling head. A circular inset shows a digital thermometer displaying -27.0°C.

350g lightweight **handle**, more ergonomic

Available in **black or white**

The image displays four handheld barcode scanners arranged in a row on a white grid background. The first two scanners are black, and the last two are white. Each scanner has a gold-colored sensor head. The black scanners have a black handle, while the white scanners have a white handle. The scanners are shown from a side profile, facing left.



755nm

More powerful energy absorption by the melanin chromophore, making it ideal for the widest range of hair types and color
- especially light-colored and thin hair

808/810nm

Deep penetration of the hair follicle with high average power with high repetition rate for fast treatment. moderate melanin absorption level making it safe for darker skin types.
ideal for treating the arms, legs, cheeks and beard.

1064nm

low melanin absorption, focused solution for darker skin types. Offers the deepest penetration of the hair follicle, embedded hair in areas as the scalp, armpit, and pubic area.

Hair removal principle

Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area



Natural hair loss, prevent regeneration, and achieve the purpose of hair removal



Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth

0000 000000 00 00 0000000 000 000000 00 0000 000000 0000 00000 00000 00000.

00000 00000 00000000 0000 000000 00000 0000 00 00

00000 00000 00000 0 0000000 000000 0000000 00000 0000 000000000 00 000000000 0000 00 00000 0000 0000.



1. 12.4 : (1
 6 (2 luanguage .
 (3 LOGO
 .
 .

1200W TEC
 1200W TEC
 1200W TEC
 1200W TEC

Energy

40 ~ 800

Frequency

12 * 20

35 * 12

-10 ~ 3

AC220/110V

1000 ~ 1200

1200W TEC

40 ~ 800

1 ~ 10

10~150 j/cm2

40 ~ 800

1 ~ 10

TEC 1200W

12 * 20

35 * 12

-10 ~ 3

12 * 20

-10 ~ 3

AC220/110V

Custom Section


CASE design



LOGO design



SYSTEM design



1200W TEC

A modern medical device showroom with various machines and a large map of China on the wall. The room features a polished floor, a grid ceiling with recessed lights, and a large map of China on the wall. The machines are arranged in a row, and the overall atmosphere is clean and professional.

OUR COUNTRIES

All the products are taking with CE/ISO certification, suitable for world market, mainly used on North America, South America, Europe. 60,000+ Customers Business development in 102+ countries...

A modern medical device showroom with various machines and a large map of China on the wall. The room features a polished floor, a grid ceiling with recessed lights, and a large map of China on the wall. The machines are arranged in a row, and the overall atmosphere is clean and professional.

OUR COUNTRIES

All the products are taking with CE/ISO certification, suitable for world market, mainly used on North America, South America, Europe. 60,000+ Customers Business development in 102+ countries...

.000000 000000 0 0000 0 0000000000 000 000000 000000 000 000 0000 000000 000 000000 00 00000 00 00000 00 00000000

1. Weifang Mingliangkj electronics Co., Ltd (company: MLKJ) 15 years of experience in the field of electronic equipment packaging and transportation. We have a professional packaging team and a mature packaging process. We can provide you with a safe and thoughtful packaging service.

2. We have a professional packaging team and a mature packaging process. We can provide you with a safe and thoughtful packaging service.

3. We have a professional packaging team and a mature packaging process. We can provide you with a safe and thoughtful packaging service.

PACKING

safe and thoughtful packaging service



Tight packaging

Training:
 (video + manual + online service)
 can keep you operate it easily

Built-in prevention collision bubble

Two-year warranty for machine
 handle as consumable,
 one-year warranty



3-5 business days delivery

professional guide:
 24 hours professional online
 customer service

