

4 in 1





**MULTI-FUNCTION
4 IN 1 MACHINE**

□□□□□□ □□□□□□

Real shot display



808 handle



Elight handle



ND YAG Laser handle



RF handle



□□□□□ □□□□ Elight / IPL Nd yag RF□ 4 □□□□□□ □□ □□ □□□□□ □□□□

1 □□ 4 □□□ RF Elight IPL □□□ □□□□ □□□□ □□□□ nd □□□□ □□□□□ □□□□□ □□ □□□□□ □□□□□ □□□□□

*.□□□ □□ □□□□□□□ □□□ □□□□□□□ 50 □□□□ □□□□□□□ □□□□□ □□□□ □□□□ □□ □□□□□ □□□□ □□□□ □□□□□

□□□□ * Elight □□□ 30,000-150,000 □□□□ □□ □□□□□□□ □□□□□□□ □□□□ □□

*Nd yag: 1064 □□□□□□ □□□□ □□□□□□□ □□ 5 □□ □□□□nm/532nm□ 1064 □□□□nm/532nm□ □□□□ □□□□ 1320nm.

*RF : □□□□ □□□□ □□□ □□□□□ □□□□ □□□□□ □ □□□ □□□ □□□□ □□□□□ □□ 6 □□ □□□□.

DIODE LASER

755/808/1064nm diode laser, for all type skin hair removal, painless



ADVANTAGE

- **PAINLESS:** 755/808/1064nm diode laser for all type skin hair removal
- **FASTER:** Large area spot sliding operation
- **NO TRAUMA:** There is no trauma to skin tissue
- **SAFETY:** To avoid the light of the deputy to reduce the difficulty of operation



Suitable for hair removal on any part of the body,
Such as arms, legs, face, armpits, back, chest, etc.



• *Cooling effect* •

The handle is frosted for one minute,
making your treatment more comfortable and painless



Elight handle



specification

- High-quality: Elight handpiece with super cooling system
- Optional Spot Size 15*50mm
- Long shots time: 150000 times
- 7 filters: 420/510/560/585/640/690/755nm
Standard: 420/510/680nm



HANDLE-ADVANTAGE



specification

- **Multiple choice**
fixed 1064nm & 532nm, adjustable 1064nm & 532nm (adjust 1-7 mm) for tattoo removal, nevus removal etc.
- **Multifunction**
1320nm for skin rejuvenation
- **Indicator light**
Dot position is the indicator light position dot more accurate



Adjustable
532nm



Adjustable
1064nm



Black doll
1320nm



Fixed
532nm



Fixed
1064nm



Before&after compare



before



One cycle



Two cycles



Three cycles

Tattoo removal



Tattoo removal



Nevus of Ota removal



Tattoo on brow removal



Lioline removal



Lioline removal



Tattoo on brow removal



RF Handl^e



12mm
eye-rf

28mm small
tripolar rf head

36mm big
tripolar rf head

14mm
bipolar-rf

28mm
bipolar-rf

38mm
bipolar-rf

Skin rejuvenation/Vascular/Acne



before



after



before



after



before



after

BEFORE & AFTE®



Hair removal



Skin rejuvenation



Freckle removal



Acne removal



Vascular



Lose weight

SCREEN INTERFAC

Professional Screen, Easy operation



測試點 測試 測試點	測試點 測試 測試點 14 測試 測試點 測試
測試 測試 測試	10-300 測試測試測試
測試測試	1-10 測試
測試 測試測試	測試 測試 50*15 :測試 測試 測試 35 * 12 測試 測試 20 * 12 :測試測試 測試
測試測試	1-150J/cm2
測試點 測試	測試測試測試 測試測試 測試 測試測試 測試 測試測試 測試 測試 測試 測試 測試 TEC

Power supply	AC220V/110V 50HZ/60HZ
Product size	113*65*76 cm Product weight
Material	Aluminum alloy frame Glass
Installation	2 people





Authentication

CE, NQA13485, CB certification
and more Complete certification
materials



60000+ Customers

We have professional after sale
team and we provide 7*24
services



2 Years Warranty

2 years warranty for each
machine, All questions will get
reponse within 24 hours



CERTIFICATE DISPLAY



00000000 00 000 000000 000000 00 00000 0000 00 00 00 00 000 000000 0000000 00 00
 000000 .0000 000000 000 000000 DHL UPS TNT FEDEX... 00000000 0000 0 0000 0 .000 00000 00

[illegible]