



# V26

Super comfortable experience  
 Painless and permanent treatment result  
 Suitable for all skin types and body areas

1. 40,000,000. 40,000,000. 40,000,000. 40,000,000. 40,000,000.
2. 40,000,000. 40,000,000. 40,000,000. 40,000,000. 40,000,000.
3. 40,000,000. 40,000,000. 40,000,000. 40,000,000. 40,000,000.
4. 40,000,000. 40,000,000. 40,000,000. 40,000,000. 40,000,000.
5. 40,000,000. 40,000,000. 40,000,000. 40,000,000. 40,000,000.
6. 40,000,000. 40,000,000. 40,000,000. 40,000,000. 40,000,000.



TEC 24

One minute cooling -21°C



## Best **TEC Cooling** system hair remover laser



- 1) 10 .mm .mmmmmm 40-10 .mmmmmm 16 / .mmmmmm 12 / .mmmmmm
- .mmmmmm .mmmmmm .mmmmmm .mmmm .mmmm .mmmm .mmmm 35 \* 12 / .mmmm .mmmmmm 20 \* 12 .mmmmmm .mmmmmm (2
- .mmmmmm .mmmmmm .mmmmmm .mmmm .mmmmmm .mmmm .mmmmmm .mmmm .mmmmmm .mmmmmm .mmmmmmmmmmmm (3.
- 4) .mmmm .mmmm .mmmmmm .mmmmmm .mm .mm .mmmmmm .mmmmmm .mm .mmmm .mmmmmm .mmmmmm.
- 5) .mmmmmm .mmmmmm .mmmmmm .mmmm 350 .mmmmmmmm .mm .mmmmmmmm .mmmmmm.



**1 minute**  
and you're done

35mm {

**FASTER**

□□□□ □□□ □□□□



1. .000000 000000 000000 14 0000 0000 000000 00000
- .000000 0000 0000 0000 6 0000 000000 0000/0000 .2
- .00000000 00 00 00000 00 000000 00000 000000 000000 6 .3
- 00000000 00000000 000000 .4 OEM (000000/000000...)

0000 0000	0000 16 000000 12 0000 10 0000 8 000000000 00000000/0000000
0000 0000	755 00000000 808 00 00 /000000000 1064 00000000 808 000000000
000000	0-150J/cm2
00000000	1-10 0000
00000 0000	40-800 0000000000
0000 LCD 00000000	14.0 0000 000000 0000 TFT True Color LCD
000000 0000 000000	000000 0000 0000 0000 000000 0000 0000 00 00000 00 0 0000 000000 00
00000	4000 0000
0000 0000	220 0000 60 / 0000 110 00 00000 50 / 0000
N.W/G.W	62 00000000 78 / 000000000

**Standardized  
production**



**Professional  
Production R & D  
Sales Department**



**Mass production  
of various styles**



- >>OEM your own machine body.
- >>OEM your own program software.
- >>OEM pretty machine colors.
- >>Print your LOGO on machine body and screen.

## Custom Section


**CASE** design



**LOGO** design



**SYSTEM** design



# CERTIFICATE DISPLAY

