



EXFU VIOLIN Portable Hair Removal Laser



Simple • Safe • Enjoy
Redefine hair removal equipment



one-button start



Ice hair removal



super power



40million shine

□□□□□□ □□□□□□

Ingenious details I am better than others

Product detail
layout



Surround light strip

Cool lighting effect
not dazzling



Newest design handle 0.31kg

One minute cooling
Customizable glowing logo



One-of-a-kind styling

Ingenious production
focus on details



1200W/1800W 1200W/1800W

1200W/1800W 1200W/1800W 1200W/1800W 1200W/1800W

1200W/1800W 36 * 12 24 * 12 1200W/1800W

* 285 1200W/1800W 1200W/1800W 1200W/1800W 1200W/1800W

* 1200W/1800W 1200W/1800W 1200W/1800W (1200W/1800W) 1200W/1800W 1200W/1800W 1200W/1800W 1200W/1800W 1200W/1800W

1 1200W/1800W 1200W/1800W 1200W/1800W 1200W/1800W 1200W/1800W



Two colors, two spot sizes are optional



Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...

7558081064nm




ALEX 755nm
For white skin
 (fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
 (brown hair removal)



YAG 1064nm
For black skin
 (black hair removal)



1. 1200-800 12-8
 2. 4 14 K
 3. 808nm 755nm 808nm 1064nm
 4. 50
 5. 10-150 j/cm2
 6. 1-10
 7. TEC

□□□□ 3500 □□□
□□□□ □□□□□□ 12*24mm 36*12 □□mm □□□□□□ □□□□□
□□□□□□ 110 □□□□□□ □□□□ □□□□ 50 / □□□□ 220 □□ □□□□ 60 / □□□□

1064 808 755 □□□□□ □□□□□

□□□□ □□□□□ □□□□□ □□□□ □□□□□□□

□□□□□□□□ 808 □□□□□ □□□□□

□□□□□□□□ 808 □□□□□ □□□□ □□□□ □□□□ □□□□□□□

□□□□□□□□ 808 □□□□□ □□□□ □□□□□□□

!□□□□□□ 24 * 7 □□□□□□ □□□□□□
□□□□□□ □□□ □□□□□□□ □□!