

MLKJ

CUSTOMER SERVICE

15 YEARS FACTORY, 2 YEARS WARRANTY, 102 COUNTRIES, 60,000+ CUSTOMERS.

MLKJ—MAKE YOUR BEAUTY BUSINESS EASIER



15 years factory



2 years warranty



102 COUNTRIES



2 years warranty



14 inch
Screen Size



3000W
Input power



1-10HZ
Frequency



755nm 808nm 1064nm
Wavelength

>>Machine 14-inch large screen

>>3000 W machine power to ensure the treatment effect

>>1-10 Hz fast frequency and 15x25mm treatment area ensures faster, smooth and effective treatment

>>808 single wave or 755nm/808nm/1064nm perfect triple wavelength

>>Easy to operate Data Base system, can do the treatment by man mode and women mode, easy to operate

350g lightweight handle, more ergonomic

>> Long life time More than 40 millions gold laser diode module, anti high temperature.

350g lightweight **handle**, more ergonomic

Available in **black or white**



350g lightweight handle, more ergonomic

>>12 pieces or 16 pieces Germany Dilas original laser bars,600/800W/1200W power is capable to meet all demands of hair removal on the whole body;

>>1-10Hz fast frequency and 15x25mm spot size ensures faster, smooth and effective treatment;
 >Super sapphire touch 蓝宝石蓝宝石系统 ensures painless and comfortable treatment;

Hair removal principle

Make Your Beauty Business More Easier





The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area

Natural hair loss, prevent regeneration, and achieve the purpose of hair removal

Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth





- 755 nm for white skin (fine, golden hair removal);
- 808 nm for yellow neutral skin (brown hair removal);
- 1064 nm for black skin (black hair removal)

蓝宝石蓝宝石系统 蓝宝石蓝宝石系统 40-20 蓝宝石蓝宝石系统 蓝宝石蓝宝石系统

蓝宝石蓝宝石系统 蓝宝石蓝宝石系统 蓝宝石蓝宝石系统 蓝宝石蓝宝石系统 :蓝宝石蓝宝石系统 808 蓝宝石蓝宝石系统
 蓝宝石蓝宝石系统 蓝宝石蓝宝石系统 蓝宝石蓝宝石系统 蓝宝石蓝宝石系统 蓝宝石蓝宝石系统 :蓝宝石蓝宝石系统 755 蓝宝石蓝宝石系统
 蓝宝石蓝宝石系统 蓝宝石蓝宝石系统 蓝宝石蓝宝石系统 蓝宝石蓝宝石系统 蓝宝石蓝宝石系统 蓝宝石蓝宝石系统 :蓝宝石蓝宝石系统 1064 蓝宝石蓝宝石系统 蓝宝石蓝宝石系统 ipl shr opt / nd yag
 / 蓝宝石蓝宝石系统 蓝宝石蓝宝石系统 蓝宝石蓝宝石系统 蓝宝石蓝宝石系统 蓝宝石蓝宝石系统







品牌	808 蓝宝石 蓝宝石V27
波长 范围	755/808/1064 nm 3 个 波长 808 蓝宝石 蓝宝石
蓝宝石 蓝宝石	蓝宝石 14 蓝宝石 蓝宝石 蓝宝石 蓝宝石
Wavelength	808nm/7558081064
shots	20-40 蓝宝石 蓝宝石
蓝宝石	10 ~ 150 j/cm2 蓝宝石 蓝宝石
Frequency	1-10HZ
Cooling	蓝宝石 蓝宝石 TEC
Power	3000W
Spot size	12 * 35 蓝宝石 蓝宝石 20 * 12 蓝宝石 蓝宝石
蓝宝石	110 蓝宝石 蓝宝石 50 / 蓝宝石 220 蓝宝石 60 / 蓝宝石
蓝宝石 蓝宝石	

1. 品牌 Weifang Mingliang 蓝宝石 蓝宝石 蓝宝石 蓝宝石 蓝宝石 蓝宝石 蓝宝石 蓝宝石 15 蓝宝石
 蓝宝石 蓝宝石 蓝宝石 蓝宝石 蓝宝石 蓝宝石 蓝宝石 蓝宝石 600000 蓝宝石 蓝宝石 蓝宝石 蓝宝石 102 蓝宝石

Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

24小时专业在线客服
24小时专业在线客服