




NEW

Portable Diode Laser





000000

10 0000 0000 00 0000 000000 *bars/15bar 000 000 0000

.0000 0000 0000 0000 00 0000 000 3 00 000 000000 50 00 000 *

000 0000000 0000 0000 000 000 1 00 3 00000000 755 0000000 808 0000000 1064 000 3 *

00000000 00000000

Mini Portable

The net weight of the handle is
about equal to one iphone

285g

Ergonomic handle
It's not tiring to take off



1200W/1800W 手持式 电吹风 迷你 便携

1200W/1800W 手持式 电吹风 迷你 便携

尺寸 36*12 重量 24*12 材质 塑料

* 285 克重量 手持式 电吹风 迷你 便携 材质 塑料


* 手持式 电吹风 迷你 便携 重量 24*12 克 (重量 24*12 克) 材质 塑料 重量 24*12 克 重量 24*12 克

EXFU

Exfu Violin

One-of-a-kind styling
Build your own hair removal machine

One minute cooling, 12x24cm²super cool area.
Newest design handle 0.31kg





800/1000/1200/1600W

50 Million Shots

USA / Germany Imported Laser Bar

755nm+808nm+1064nm



ALEX 755nm
For white skin
(fine, golden hair removal)






SPEED 810nm
For yellow neutral skin
(brown hair removal)



YAG 1064nm
For black skin
(black hair removal)

7558081064nm 0000 00000 0000 00000 00000 000 0000 000000





Ingenious details I am better than others

Product detail
layout



Surround light strip

Cool lighting effect
not dazzling



Newest design handle 0.31kg

One minute cooling
Customizable glowing logo



One-of-a-kind styling

Ingenious production
focus on details



