



1. CE ISO13485 2. 3. 4. 5. 6. 7. 8. 9. 10. 11. 12. 13. 14. 15. 16. 17. 18. 19. 20. 21. 22. 23. 24. 25. 26. 27. 28. 29. 30. 31. 32. 33. 34. 35. 36. 37. 38. 39. 40. 41. 42. 43. 44. 45. 46. 47. 48. 49. 50. 51. 52. 53. 54. 55. 56. 57. 58. 59. 60. 61. 62. 63. 64. 65. 66. 67. 68. 69. 70. 71. 72. 73. 74. 75. 76. 77. 78. 79. 80. 81. 82. 83. 84. 85. 86. 87. 88. 89. 90. 91. 92. 93. 94. 95. 96. 97. 98. 99. 100.



1. .
2. .
3. .
4. .

1600 1200 1000

One minute cooling -27°C

Best **TEC Cooling** system hair remover laser



1600 1200 1000

. 20*1.12

35 * 2.12

.3

350g lightweight **handle**, more ergonomic

Available in **black or white**




>>Germany Emitter, strong

1200<<W power of hair removal on the whole body;

>>1-10Hz fast

>> Italy water pump, it can keep machine working 24 hours without stop.



755nm

More powerful energy absorption by the melanin chromophore, making it ideal for the widest range of hair types and color
- especially light-colored and thin hair

808/810nm

Deep penetration of the hair follicle with high average power with high repetition rate for **fast treatment**. moderate melanin absorption level making it **safe for darker skin types**.
ideal for treating the arms, legs, cheeks and beard.

1064nm

low melanin absorption, focused solution for darker skin types. Offers the **deepest penetration** of the hair follicle, embedded hair in areas as the scalp, armpit, and pubic area.

Hair removal principle

Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area



Natural hair loss, prevent regeneration, and achieve the purpose of hair removal



Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth

0000 000000 00 00 0000000 000 000000 00 0000 000000 0000 00000 00000 00000.

00000 00000 00000000 0000 000000 00000 0000 00 00

00000 00000 00000 0 0000000 000000 0000000 00000 0000 000000000 00 000000000 0000 00 00000 0000 0000.



00000 0000 000000



The new 14-inch screen is clear
easy to operate.



OEM/ODM SEVRICE

3D LOGO with luxurious texture.

1). 12.4 inch screen


6 (2 language)

3 LOGO with luxurious texture

12.4 inch screen	12.4 inch screen
6 (2 language)	6 (2 language)
3 LOGO with luxurious texture	3 LOGO with luxurious texture
12 * 20 mm applicator	12 * 20 mm applicator
12 * 35 mm applicator	12 * 35 mm applicator
1000 ~ 1200 J/cm² energy	1000 ~ 1200 J/cm² energy
12 * 20 mm applicator	12 * 20 mm applicator
40 ~ 800 J/cm² energy	40 ~ 800 J/cm² energy
1 ~ 10 Hz frequency	1 ~ 10 Hz frequency
TEC 1200W	TEC 1200W
12 * 20 mm applicator	12 * 20 mm applicator
35 * 12 mm applicator	35 * 12 mm applicator
-10 ~ 3 °C temperature	-10 ~ 3 °C temperature
AC220/110V 50/60HZ	AC220/110V 50/60HZ

Custom Section


CASE design



LOGO design



SYSTEM design



0000 00000

OUR TEAM

There are more than 100 members of production team in our factory.





mingliangkj:

Weifang Mingliang electronics Co., Ltd (简称为:MLKJ) 专业从事 各种 医疗设备 的 研发 生产 销售 服务 等 业务 的 企业。

. 公司拥有 先进 的 生产设备 和 技术 人员 , 能够 承接 各种 医疗设备 的 研发 生产 销售 服务 等 业务 。 公司 产品 主要 用于 医院 、 诊所 、 体检 中心 等 场所 。 公司 产品 主要 有 : 各种 医疗设备 、 各种 医疗设备 配件 、 各种 医疗设备 维修 服务等 。

公司 产品 主要 用于 医院 、 诊所 、 体检 中心 等 场所 。 公司 产品 主要 有 : 各种 医疗设备 、 各种 医疗设备 配件 、 各种 医疗设备 维修 服务等 。

公司 产品 主要 用于 医院 、 诊所 、 体检 中心 等 场所 。

1.Weifang Mingliangkj electronics Co., Ltd (简称为:MLKJ) 15 . 公司拥有 先进 的 生产设备 和 技术 人员

公司 产品 主要 用于 医院 、 诊所 、 体检 中心 等 场所 。 公司 产品 主要 有 : 各种 医疗设备 、 各种 医疗设备 配件 、 各种 医疗设备 维修 服务等 。

公司 产品 主要 用于 医院 、 诊所 、 体检 中心 等 场所 。 公司 产品 主要 有 : 各种 医疗设备 、 各种 医疗设备 配件 、 各种 医疗设备 维修 服务等 。

PACKING

safe and thoughtful packaging service



Built-in prevention
collision bubble

Two- year warranty for machine
handle as consumable,
one-year warranty

Tight packaging

Training:
(video +manual+online service)
can keep you operate it easily



3-5 business days
delivery

professional guide:
24 hours professional online
customer service