



□□□□□

10 □□□□ □□□□ □□□□ □□ □□□□ □□□□□ *bars/15bar □□□ □□□ □□□□

.□□□□ □□□□ □□□□ □□□□ □□ □□□□ □□□□ 3 □□ □□□ □□□□□ □□□□□ 50 □□ □□□ *

□□□ □□□□□□□ □□□□ □□□□ □□□ □□□ □□□ □□□□□□□ 755 □□□□□□□ 808 □□□□□□□ 1064 □□□□ □□□ 3 *



EXFU VIOLIN Portable Hair Removal Laser



Simple • Safe • Enjoy
Redefine hair removal equipment



one-button start



Ice hair removal



super power



40million shine

□□□□□□ □□□□□□

Ingenious details I am better than others

Product detail
layout



Surround light strip

Cool lighting effect
not dazzling



Newest design handle 0.31kg

One minute cooling
Customizable glowing logo



One-of-a-kind styling

Ingenious production
focus on details



□□□□ □□□□□□

1200W/1800W □□□□□□ □□□□□□ □□□□ □□□□ □□□□

□□□ □□□□ 36*12 □□ 24*12 □□□□ □□□□□□

* 285 □□□□□□ □□□□□□ □□□□ □□□□□□ □□□□ □□□ □□□□ □□□□ □□□

* □□□□ □□□□□□□□ □□□□ □□□□ □□ □(□□□□□ □ □□□□□□□ □□□) □□□ □□□□□□ □□□□ □□□□ □□□□ □□□□ □□□□ □□□□ □□□□ □□□□ □□□ □□

1 □□□ □□□□ □ □□□□ □□□□□□ □□□□□ □□□□□ □□□□ □□ □□ □□□□□□



Two colors, two spot sizes are optional



Suitable for any unwanted hair on areas like face, arms, armpits, chest, back, bikini, legs...

7558081064nm




ALEX 755nm
For white skin
 (fine, golden hair removal)



SPEED 810nm
For yellow neutral skin
 (brown hair removal)



YAG 1064nm
For black skin
 (black hair removal)



1. 755nm 808nm 1064nm
 2. 1200---800 12---8 1200---800/1000
 3. 4 14 1000K 1000
 4. 808nm 755 nm 808nm 1064nm
 5. 50 1000
 6. 10~150 j/cm2 1000
 7. 1-10 1000

TEC 3500 12*24mm 36*12 mm 110 50 / 220 60 /

1064 808 755

808

808

808

808

! 24 * 7