



FASTER, STRONGER, SMARTER

මමගේ මම මමගේ මම TEC මම මමගේ මම මමගේ මම මමගේ මම මමගේ මම මම මම මම. 24 මම මම මමගේ මමගේ .මම මමගේ මම .මම මම මම!

1 minute
and you're done

35mm {

FASTER

1. 14

2. 6

3. 6

4. OEM ()

16 12 10 8

755 808 1064 808

0-150J/cm²

1-10

40-800

14.0 TFT True Color LCD

4000

220 60 / 110 50 /

4000

220 60 / 110 50 /

N.W/G.W 62 78 /


Company Strength



- >>OEM your own machine body.
- >>OEM your own program software.
- >>OEM pretty machine colors.
- >>Print your LOGO on machine body and screen.

Custom Section


CASE design



LOGO design



SYSTEM design



□□□□ □□□□

CERTIFICATE DISPLAY



Packing

safe and thoughtful packaging service



Built-in prevention Collision bubble

Two-year warranty for machine handle as consumable,
one-year warranty.

OEM&ODM service for distributor.

Tight packaging

Training: (Video+Manual+Online Service)
Can Keep You Operate It Easily.



3-5 business days delivery

Professional guide:
24 Hours Professional online customer service,

