

1600 1200 1000

One minute cooling -27°C

Best **TEC Cooling** system
hair remover laser




20*1.12 35 * 2.12 .3

350g lightweight **handle**, more ergonomic

Available in **black or white**





- >>Germany Emitter, strong
- 1200<<W power of hair removal on the whole body;
- >>1-10Hz fast
- >> Italy water pump, it can keep machine working 24 hours without stop.



755nm

1064nm

Hair removal principle

[illegible]

111

□ □ □ □ □ □ □ □

□ □ □ □ □ □ □ □

☐	☐	☐	☐	☐	☐	☐	☐	☐	☐
--------------------------	--------------------------	--------------------------	--------------------------	--------------------------	--------------------------	--------------------------	--------------------------	--------------------------	--------------------------

□ □ □ □ □ □ □ □ □ □ □ □ □ □ □

Energy

□ □ □ □ □ □ □ □ □ □

Frequency

□□□□□ □□□ □□□□□

□ □ □ □ □ □ □ □

□ □ □ □ □ □ □ □ □ □

□ □ □ □ □ □ □ □ □ □

□□□□□□□□ □□□□ □□□□□□ □□□□ □□□□□□□□

12 000000 00 00000000 0000 1000 000 10 0000 1200 0000

□□□□ □□□ □□□□ □□□□ 12 □□□□ □□□□

40 □□□ □□□□□□

10~150 j/cm2 □ □□□□ □□□□

40 ~ 800 ㎜㎜㎜ ㎜㎜㎜ ㎜㎜㎜㎜ ㎜㎜㎜

1 □□□□ 10 □□

TEC 1200W

□□□□□□ □□ □□ □□□□ □ □□□

□□□□ □□□□ □□ □□□□□□ □□

☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐ ☐

12 * 20 □□□ □□□□ 35 * 12 □□□□ □□□□

-10 ~ 3 □□□□□□□□ □□□□

AC220/110V□ 50/60HZ

Custom Section


CASE dedign



LOGO design



SYSTEM design



□ □ □ □ □ □ □ □ □


OUR TEAM

There are more than 100 members of production team in our factory.



OUR COUNTRIES

All the products are taking with CE/ISO certification ,suitable for world market ,
mainly used on North America ,
South America Europe
60, 000+ Customers Business development
in 102+ countries...



Customer visit



mingliangkj:

1.Weifang Mingliangkj electronics Co., Ltd (:MLKJ) 15 .

2. .

3. .

PACKING

safe and thoughtful packaging service



Built-in prevention
collision bubble

Two- year warranty for machine
handle as consumable,
one-year warranty

Tight packaging

Training:
(video +manual+online service)
can keep you operate it easily



3-5 business days
delivery

professional guide:
24 hours professional online
customer service