




1. 14-inci HD 4K ekran, 2. TEC teknolojisi, 3. 1064 nm lazer, 4. 808 nm lazer, 5. 755 nm lazer.

1. 14-inci HD 4K ekran, 2. TEC teknolojisi, 3. 1064 nm lazer, 4. 808 nm lazer, 5. 755 nm lazer.
2. 14-inci HD 4K ekran, 2. TEC teknolojisi, 3. 1064 nm lazer, 4. 808 nm lazer, 5. 755 nm lazer.
3. 14-inci HD 4K ekran, 2. TEC teknolojisi, 3. 1064 nm lazer, 4. 808 nm lazer, 5. 755 nm lazer.
4. 14-inci HD 4K ekran, 2. TEC teknolojisi, 3. 1064 nm lazer, 4. 808 nm lazer, 5. 755 nm lazer.
5. 14-inci HD 4K ekran, 2. TEC teknolojisi, 3. 1064 nm lazer, 4. 808 nm lazer, 5. 755 nm lazer.






Laser show Handle laser bar optional



⊙ 10bar


⊙ 12bar

⊙ 16bar



Working Principle

Suits for all skin and hair types




- **755nm for white skin** (fine, golden hair removal)
- **808nm for yellow neutral skin** (brown hair removal)
- **1064nm for black skin** (black hair removal)



□□□□ □□□□□□

Treatment Comparison



.0000 00000 00 00 00000 000000 0000 0000
000000 0000 24!