

# DIODE LASER hair removal machine

■ 2 Years Warranty ■ OEM / ODM Service ■ 3 waves 1064nm +808nm + 755nm



DIODE LASER hair removal machine **D10**

\* 12--8 treatment sessions are required for permanent hair removal.

\* The treatment area is limited to 30cm x 30cm, and the treatment time is 50 minutes.

\* 3 wave diode laser hair removal machine 1 755nm diode laser 808nm diode laser 1064nm diode laser

## Handle Display

Two colors, two spot sizes are optional



1064nm 808nm 755nm : all skin and hair types

755nm suits for all skin and hair types.

808nm suits for all skin and hair types.

1064nm suits for all skin and hair types.

## *Working Principle*

755nm and 808nm and 1064nm , suits for all skin and hair types.



**ALEX 755nm**  
**For white skin**  
(fine, golden hair removal )



**SPEED 810nm**  
**For yellow neutral skin**  
(brown hair removal)



**YAG 1064nm**  
**For black skin**  
(black hair removal)

# The real experience is visible

Through live test verification ,safe ,long,painless  
and effective



- 1) .000 00 0000000 00000 14 0000 0000 00000 0000 :0000 0000000  
.000 0000 0000 00000 00000 00000 000 00 :0000000 0000 (2  
00000 (3 OEM: 00 000 000 00000 0000 000000 000000 00000 00 00000 0000 00 0000 00 00 0000 0000  
0000000.





# Product details

Ultra-thin large screen, cool light strip



!!!!! 24!