

5 in 1

BODY SHAPING SYSTEM

- ◎ Roller mechanical massage
- ◎ Vacuum negative pressure adsorption
- ◎ Bipolar radiofrequency thermal
- ◎ Near infrared laser



Advantage

5 treatment handles

According to different treatment areas, treatment items, treatment demands, etc., it can easily achieve perfect body shaping, local slimming and weight loss, skin tightening and lifting, skin texture improvement, etc.

Perfect control system

Adsorption strength, adsorption frequency, roller speed, roller direction, red light intensity, radio frequency power, etc., can be freely adjusted to meet various treatment demands of patients.

True dual-monopolar radio frequency system


The dual-monopolar radio frequency system using Korean 6M radio frequency power supply effectively avoids epidermal burns. The radio frequency energy acts more concentratedly on the target tissue (dermis and subcutaneous tissue), resulting in less pain during treatment. , the number of treatments is significantly reduced.

80 **K:** "The body shaping system" is a professional body shaping device. It can achieve perfect body shaping, local slimming and weight loss, skin tightening and lifting, skin texture improvement, etc. according to different treatment areas, treatment items, treatment demands, etc. It can be easily adjusted to meet various treatment demands of patients. The dual-monopolar radio frequency system using Korean 6M radio frequency power supply effectively avoids epidermal burns. The radio frequency energy acts more concentratedly on the target tissue (dermis and subcutaneous tissue), resulting in less pain during treatment. , the number of treatments is significantly reduced.



RF The body shaping system is a professional body shaping device. It can achieve perfect body shaping, local slimming and weight loss, skin tightening and lifting, skin texture improvement, etc. according to different treatment areas, treatment items, treatment demands, etc. It can be easily adjusted to meet various treatment demands of patients. The dual-monopolar radio frequency system using Korean 6M radio frequency power supply effectively avoids epidermal burns. The radio frequency energy acts more concentratedly on the target tissue (dermis and subcutaneous tissue), resulting in less pain during treatment. , the number of treatments is significantly reduced.

RF: The body shaping system is a professional body shaping device. It can achieve perfect body shaping, local slimming and weight loss, skin tightening and lifting, skin texture improvement, etc. according to different treatment areas, treatment items, treatment demands, etc. It can be easily adjusted to meet various treatment demands of patients. The dual-monopolar radio frequency system using Korean 6M radio frequency power supply effectively avoids epidermal burns. The radio frequency energy acts more concentratedly on the target tissue (dermis and subcutaneous tissue), resulting in less pain during treatment. , the number of treatments is significantly reduced.


Working principle



1 Pumping, relaxing, and pressing through vacuum vacuum suction



3 Reuse 940nm infrared to effectively reduce fat cells



4 Then use the roller or massage to dissolve deep fat, clear the lymph, eliminate toxins, eliminate edema



5 Use 10MHz RF to tighten and enhance skin after weight loss



6 Finally, the orange peel is faded, the curve is attractive, and the skin is smooth and smooth.

Working principle



Large handle with vacuum roller+RF+IR
For large area such as thigh, buttock waist and abdomen.



Medium handle, vacuum roller+RF+IR, button control
For small area, such as arms, flanks.



Small handle, vacuum +RF
For face, forehead and neck.



Smallest handle, vacuum +RF
For eyes.



Large 40KHz cavitation handle
For all body slimming.

1. 2.8mm vacuum roller

2. 2.8mm vacuum roller with 10MHz RF+IR technology

3. 2.8mm vacuum roller with 10MHz RF+IR technology and button control

4. 2.8mm vacuum roller with 10MHz RF+IR technology and button control

5. 2.8mm vacuum roller

6. 2.8mm vacuum roller with 10MHz RF+IR technology and button control

7. 2.8mm vacuum roller with 10MHz RF+IR technology and button control

Treatment efficacy



Body shaping




Dissolves fat and improves skin




Improve stretch marks



Dissolves fat and improves skin



Create a V face



Relieve joint pain









000000 0000 000000

* 000000 0000000 0000000 14 0000 000000 0000

000000 000000 0 000000 0000 0000 0000000 000000 000000 *

0000000 00 000000000 000000000 000000*


000000 000000 00000000 00000000 000000 0000000 000000000 *

1 4-inch HD screen

Smarter and safer screen system



Machine introduction



! 24*7 !