

Exceeding your expectations

The most professional beauty machine customization service

Surrounded by a whole set of services

Making the purchasing experience wonderful



24-Hour online
After-sales service



15 Years Laser Beauty
Device Manufacturer



OEM Factories
Support customization

0000 00 00000000 0000 00 00000 000000 00000000 00 000000 00000000 00000 0000 000000
00000000 00000000 00000 00000000 0000000 000000 00 00000 00000 0000000000 00 000000

EXFU Seiko



11D HIFU

Macro & Micro High Intensity Focused Ultrasound System



SAFE



EFFECTIVE




MULTI-DEPTH



11 EXFU Seiko 11D HIFU Macro & Micro High Intensity Focused Ultrasound System

EXFU Seiko 11D HIFU





Macro & Micro High Intensity Focused Ultrasound System

7 CARTRIDGES + 4 GUN HEADS


1.5mm, 2.0mm, 3.0mm, 4.5mm for face treatment
6.0mm, 9mm, 13mm for body treatment.



MF2.0MM


Unique ultra-thin probe Clexis patented technology

"Special cartridge for eyes treatment"



MF2.0MM is a non-invasive laser treatment for the eyes. It uses a unique ultra-thin probe (0.5-0.8mm) to deliver laser energy to the eye area. This treatment is designed to improve the appearance of the eye area, including the eyelids and the area around the eyes. The probe is designed to be gentle on the skin and does not require anesthesia. The treatment is performed in a series of passes, and the results are visible immediately. MF2.0MM is a safe and effective treatment for the eyes, and it is suitable for all skin types. The treatment is performed in a series of passes, and the results are visible immediately. MF2.0MM is a safe and effective treatment for the eyes, and it is suitable for all skin types.

Body Treatment



• *Treatment Effect* •



□□□	□□□□□ □□□□ 7 □□□□□ □□ □□□□□ □□□□□□□□□□
□□□	□□□□ □□□ □□ □□□□□ □□□□□□□□□□

□□ □□□□□□	□□□ □□□□ 4.5 □□□□ □□□□ 3.0 □□□□ □□□□ 1.5 :□□□□
□□□□ □□□□□□	7D HF: MF2/6/9/13 L4-4.5 L7-1.5 L7-3.0
□□□□□ □□□□□	0.1J-2.5J (0.1J □□□□□□ □□ □□)
□□□□ □□ □□□□□	1.0mm-4.0mm
□□□ □□□	5-25 □□□ □□□□□
□□ □□□	□□□ 300000 □□□□□□□□ □□
□□□□□ □□□□ □□□□□□	15 □□□□
□□□□□□	110V-240V□ 50/60Hz



- □□□□ □□□□□ □□□□ □□□□ □□□□□□□□□□
- □□□□□ □□□□□□□ 15.6 □□□□ □□□□ □□□□□ □□□□ .1
- .□□□□□ □□□□ □□□□ □□□□ 6 □□□□ □□□□□ □□□□□□ .2
- .□□□□ □□□□□ □□□□ □□□□□□□□□□ .3
- □□□□□ .4 OEM □□□□□□□□□□) □□□□□□□□□□...
- □□□ □□□□□□ □□□□□□ □□□□□□□□ □□ □□□□□□ □□□□□!