


2in1 machine



Picosecond handle



550mm

0000000 0 0000 0000 000000 000000 .1 000000 000000 000 00 000000 00 0000000 000 0000000 00000000 000000
000 00 0000000 000 000 000000 00.

5 TREATMENT HEADS

A solution to a variety of skin problems

532: Remove colored tattoos.

755 honeycomb head: used to remove age spots, freckles, and chloasma. little damage to skin

Adjustable parameter 1064: for tattoo removal, eyebrow clearing

Non-adjustable parameter 1064: used for removing tattoos and clearing eyebrows

1320: large area treatment, large spot, fast treatment speed and good effect



1. 1064nm (Size Optional) 2. 532nm (Original) 3. 1320nm (Blackface doll) 4. 755nm (Honeycomb) 5. 1064nm (Original)



5. 1320: large area treatment, large spot, fast treatment speed and good effect

4. 1064: adjustable parameter 1064: for tattoo removal, eyebrow clearing


3. 1064: non-adjustable parameter 1064: used for removing tattoos and clearing eyebrows

2. 532: Remove colored tattoos.


1. 755 honeycomb head: used to remove age spots, freckles, and chloasma. little damage to skin

5. 1320: large area treatment, large spot, fast treatment speed and good effect


Working Principle




Q. How does laser treatment work? The laser beam is directed at the skin, where it is absorbed by the pigment in the tattoo. This causes the pigment to break up into smaller particles, which are then removed by the body's immune system. The laser treatment is a non-invasive procedure that can be used to remove a variety of tattoos and skin conditions. The results are typically visible within a few weeks of treatment.



Original pigment



Traditional laser



Picosecond Laser



BEFORE



AFTER

DIODE LASER

755/808/1064nm diode laser, for all type skin hair removal, painless



755nm



808nm



1064nm



此款设备采用先进的755/808/1064nm三波长二极管激光技术，结合Nd:YAG激光，实现2 in 1功能，适用于各种肤质，无痛脱毛。

.该设备采用先进的755/808/1064nm三波长二极管激光技术，结合Nd:YAG激光，实现2 in 1功能，适用于各种肤质，无痛脱毛。*

.该设备采用先进的755/808/1064nm三波长二极管激光技术，结合Nd:YAG激光，实现2 in 1功能，适用于各种肤质，无痛脱毛。50 分钟 *

该设备采用先进的755/808/1064nm三波长二极管激光技术，结合Nd:YAG激光，实现2 in 1功能，适用于各种肤质，无痛脱毛。1 至 3 分钟，755 波长，808 波长，1064 波长 3 *



800/1000/1200/1600W

50 Million Shots

USA / Germany Imported Laser Bar

755nm+808nm+1064nm



ALEX 755nm

For white skin

(fine, golden hair removal)



SPEED 810nm

For yellow neutral skin

(brown hair removal)



YAG 1064nm

For black skin

(black hair removal)

1. Alex 755nm 755nm 755nm 755nm 755nm

1. Alex 755nm 755nm 755nm 755nm 755nm

2. 808nm 808nm 808nm 808nm 808nm

3. 1064nm 1064nm 1064nm 1064nm 1064nm

CLINICAL EFFECT



雷射脫毛 雷射脫毛

雷射脫毛 雷射脫毛 12.1 雷射脫毛 雷射脫毛 雷射脫毛

雷射脫毛 雷射脫毛 雷射脫毛 雷射脫毛

6 雷射脫毛 雷射脫毛 雷射脫毛 雷射脫毛 雷射脫毛 雷射脫毛 雷射脫毛 雷射脫毛

雷射脫毛 OEM 雷射脫毛 / 雷射脫毛 / 雷射脫毛 雷射脫毛 雷射脫毛 雷射脫毛 雷射脫毛 雷射脫毛 雷射脫毛 雷射脫毛

