

3) 鋼 鋼板 鋼管 40 鋼管 800/1000/1200/1600 鋼 鋼板




weight **450g**
The handle weighs only 450g, making the treatment process easier

12*20mm 12*35mm 12*20mm 12*35mm

0000 00000 0000 0000 35 * 12 / 0000 0000 20 * 12 0000 0000 000000
0000 00000 I-VI 0000 0000 0 0000 0000 000000 000000 0000 000000 00000 0

Laser show Handle laser bar optional



1064nm 808nm 755nm 1064nm 808nm 755nm 1064nm 808nm 755nm

10bar 12bar 16bar

1064nm 808nm 755nm 1064nm 808nm 755nm 1064nm 808nm 755nm

000000 000000 0000 0000 000000 000000 0 0000 000000 000000 00000 00000 1064 808 755 0000 0000 3 0000 00000000
00000
000000 000000 00000
000000 000000 0000 000000 ICE PLUS. 0000 00 00000 000000 00000000.




□□□ □□□ □□□□ 24 □□□ □□ □□□□□ □□□ □□ □□□□□ □□.



Just One minute!
Quick cooling down to **-25°C**



Treatment Comparison



- 00000 0000 000000 000000 0000000
- 0000 000 0000000 14 0000 000000 00000 .1
- 0000 000 6 0000 0000 6 000 0 000 000000 0000000 00000 000 .2
- 000 000000 000000 00 000 000000 00000 000000 000000 6 .3
- 0000000 000000 .4 OEM 000/000000/00000/00000) 0000000...

FREE LOGO SERVICE





14 Years Laser Beauty Decvise Manuafactor

- High Feedback Top10 Supplier
- OEM & ODM SERVICE



本公司 14 年从事美容设备生产，拥有 14 年工厂，2 年质保，60000+ 客户，102 个国家。
 我们拥有完善的质量管理体系，确保每台设备都符合国际标准。
 我们提供 OEM 和 ODM 服务，可根据客户需求定制产品。

Certificate display

Certificate is the best guarantee for you



Packing

Safe and thoughtful packaging service



Tight packaging

The machine shall be made of waterproof materials and packaged

**Anti collision foam board
inside aluminum box**



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service

CONTACT US



In terms of following trade details:

- 1)The shipping cost are based on DHL cost to your country
- 2)Delivery time:3-5 days after receiving payments.
- 3)Payment terms:T/T(bank transfer),Western Union.
- 4)Warranty:2 years for the whole machine
- 5)Warranty Policy:one month guarantee replacement (we bear all shipping cost),2years warranty,lifelong maintenance.
- 6)Packing method: Aluminum box with hard plastic foam.
- 7)Free-training to customers:Free We could offer DVD and User's manual and 10 Hours online service to our customers
- 8)Certifications:CE TUV SFDA ISO 13485
- 9)MOQ:1 UNIT
- 10)The quotation here above is valid within 1 month