



1. CE ISO13485 2. 3. 4. 5. 6. 7. 8. 9. 10. 11. 12. 13. 14. 15. 16. 17. 18. 19. 20. 21. 22. 23. 24. 25. 26. 27. 28. 29. 30. 31. 32. 33. 34. 35. 36. 37. 38. 39. 40. 41. 42. 43. 44. 45. 46. 47. 48. 49. 50. 51. 52. 53. 54. 55. 56. 57. 58. 59. 60. 61. 62. 63. 64. 65. 66. 67. 68. 69. 70. 71. 72. 73. 74. 75. 76. 77. 78. 79. 80. 81. 82. 83. 84. 85. 86. 87. 88. 89. 90. 91. 92. 93. 94. 95. 96. 97. 98. 99. 100.



1. 2. 3. 4. 5. 6. 7. 8. 9. 10. 11. 12. 13. 14. 15. 16. 17. 18. 19. 20. 21. 22. 23. 24. 25. 26. 27. 28. 29. 30. 31. 32. 33. 34. 35. 36. 37. 38. 39. 40. 41. 42. 43. 44. 45. 46. 47. 48. 49. 50. 51. 52. 53. 54. 55. 56. 57. 58. 59. 60. 61. 62. 63. 64. 65. 66. 67. 68. 69. 70. 71. 72. 73. 74. 75. 76. 77. 78. 79. 80. 81. 82. 83. 84. 85. 86. 87. 88. 89. 90. 91. 92. 93. 94. 95. 96. 97. 98. 99. 100.

One minute cooling -27°C


Best **TEC Cooling** system  
hair remover laser

A hand wearing a white glove holds a black and white laser hair removal device. A circular inset shows a digital thermometer displaying -27.0°C, indicating the cooling effect of the TEC system.

**350g** lightweight **handle**, more ergonomic

Available in **black or white**

Four handheld barcode scanners are displayed in a row on a white grid background. The first two are black with a gold-colored sensor window, and the last two are white with a silver-colored sensor window. Each scanner has a trigger button on the handle.



755nm

**More powerful energy absorption** by the melanin chromophore, making it ideal for the widest range of hair types and color  
- especially light-colored and thin hair

808/810nm

**Deep penetration of the hair follicle with high average power** with high repetition rate for **fast treatment**. moderate melanin absorption level making it **safe for darker skin types**. ideal for treating the arms, legs, cheeks and beard.

1064nm

**low melanin absorption, focused solution for darker skin types**. Offers the **deepest penetration** of the hair follicle, embedded hair in areas as the scalp, armpit, and pubic area.

# Hair removal principle

Make Your Beauty Business More Easier



The laser selectively acts on the melanin in the hair follicle, destroying the hair-growing area



Natural hair loss, prevent regeneration, and achieve the purpose of hair removal




Hair removal also stimulates collagen regeneration, shrinks pores and makes skin firm and smooth

1. The laser energy is absorbed by the melanin in the hair shaft, which is the primary target for hair removal.

2. The absorbed energy is converted into heat, which damages the hair follicle and prevents it from regrowing.

3. The damaged hair follicle is eventually shed, and the skin surface is smoothed and firm.



WALTZ PRO LASER

|   |   |   |
|---|---|---|
|   |   |   |
| 1 | 2 | 3 |

Before After



The new 14-inch screen is clear  
easy to operate.



OEM/ODM SEVRICE

3D LOGO with luxurious texture.

12.4 inch 14 inch screen

12.4 inch screen (1

6 (2 language .

3 LOGO with luxurious texture

12

12

12

12

12

Energy

12

Frequency

12

12

12

12

12

12

12

12

40

10~150 j/cm2

40 ~ 800

1

TEC 1200W

12

12

12

12 \* 20

-10 ~ 3


AC220/110V 50/60HZ

# Custom Section


## CASE design



## LOGO design




## SYSTEM design



0000 00000

## OUR TEAM

There are more than 100 members of production team in our factory.





**mingliangkj:**

Weifang Mingliang electronics Co., Ltd (简称为:MLKJ) 专业从事 各种 医疗设备 的 研发 生产 销售 服务 等 业务 的 企业。

. 公司拥有 先进 的 生产设备 和 技术 力量 , 能够 承接 各种 医疗设备 的 研发 生产 销售 服务 等 业务 。 公司 拥有 完善 的 质量管理体系 , 产品 质量 稳定 可靠 , 价格 合理 公道 , 服务 周到 细致 , 赢得了 广大 客户 的 信任 和 支持 。

公司 拥有 完善 的 质量管理体系 , 产品 质量 稳定 可靠 , 价格 合理 公道 , 服务 周到 细致 , 赢得了 广大 客户 的 信任 和 支持 。

公司 拥有 完善 的 质量管理体系 , 产品 质量 稳定 可靠 , 价格 合理 公道 , 服务 周到 细致 , 赢得了 广大 客户 的 信任 和 支持 。

1.Weifang Mingliangkj electronics Co., Ltd (简称为:MLKJ) 15 . 公司拥有 先进 的 生产设备 和 技术 力量 , 能够 承接 各种 医疗设备 的 研发 生产 销售 服务 等 业务 。

公司拥有 先进 的 生产设备 和 技术 力量 , 能够 承接 各种 医疗设备 的 研发 生产 销售 服务 等 业务 。

公司拥有 先进 的 生产设备 和 技术 力量 , 能够 承接 各种 医疗设备 的 研发 生产 销售 服务 等 业务 。

# PACKING

safe and thoughtful packaging service



Built-in prevention  
collision bubble

Two- year warranty for machine  
handle as consumable,  
one-year warranty

Tight packaging

Training:  
(video +manual+online service)  
can keep you operate it easily



3-5 business days  
delivery

professional guide:  
24 hours professional online  
customer service