



V26

Super comfortable experience
Painless and permanent treatment result
Suitable for all skin types and body areas

1. 100% effective hair removal.
2. 40,000,000. treatments. 100% effective hair removal. 100% effective hair removal. 100% effective hair removal.
3. 100% effective hair removal. 100% effective hair removal.
4. 100% effective hair removal. 100% effective hair removal.
5. 14.0. 100% effective hair removal. 100% effective hair removal.
6. 100% effective hair removal. 100% effective hair removal.

TEC system. 24 hours. 24 hours. 24 hours.

One minute cooling -21°C

Best **TEC Cooling** system
hair remover laser

- 1) 10. 40-10. 16 / 12 / 12
- 2) 35 * 12 / 20 * 12

- 3) ...
- 4) ...
- 5) ... 350 ...

1 minute
and you're done

35mm {

FASTER

... ..

1. ... 14 ...
2. ... 6 ...
3. ... 6 ...
4. OEM (...)

...	... 16 ... 12 ... 10 ... 8 ...
...	755 ... 808 ... / ... 1064 ... 808 ...
...	0-150J/cm2
...	1-10 ...
...	40-800 ...
... LCD ...	14.0 ... TFT True Color LCD
...
...	4000 ...
... ..	220 ... 60 / ... 110 ... 50 / ...

**Standardized
production**



**Professional
Production R & D
Sales Department**



**Mass production
of various styles**



- >>OEM your own machine body.
- >>OEM your own program software.
- >>OEM pretty machine colors.
- >>Print your LOGO on machine body and screen.

Custom Section


CASE design



LOGO design



SYSTEM design



□□□□ □□□□

CERTIFICATE DISPLAY

