



# HIGH POWER DIODE LASER

755+808+1064nm  
For all skin and hair types



[Learn more details](#)

□□□□□

- .□□□ □□□ □□□□ □□□ 16--8 □□□□ □□□□ □□□□□ □□ □□□□□ □□□□□□□ \*
- .□□□□□ □□□□□ □□□□□ □□ □□□□□ □□□□□ 3 □□ □□□ □□□□□ □□□□□□□ 50 □□ □□□ \*
- □□□□□□□ □□□□ □□□□ □□□ □□□ □□□ □□□□□□□□□ 755 □□□□□□□□□ 808 □□□□□□□□□ 1064 □□□□ □□□ 3 \*





**Arm** hair removal

**Lip** hair removal

**Face** hair removal

**Leg** hair removal

**Back** hair removal

**Underarm** hair removal

**Bikini** hair removal

# DIODE LASER

755/808/1064nm diode laser, for all type skin hair removal, painless



## ADVANTAGE

- **PAINLESS:**755/808/1064nm diode laser for all type skin hair removal
- **FASTER:**Large area spot sliding operation
- **NO TRAUMA:**There is no trauma to skin tissue
- **SAFETY:**To avoid the light of the deputy to reduce the difficulty of operation



□□□□ □□□□□□

□□□□□□ □□□□□□ □□□□ □□□ 1800 □□□□ 1200 □□□□ □□□□

□□□ □□□□ 35 \* 12 □□ 20 \* 12 □□□□ □□□□□□



350 \*

\*  
□□□□

800/1000/1200/1600W  
**50 Million Shots**  
 USA / Germany Imported Laser Bar

**755nm+808nm+1064nm**



**ALEX 755nm**  
**For white skin**  
 (fine, golden hair removal )



**SPEED 810nm**  
**For yellow neutral skin**  
 (brown hair removal)



**YAG 1064nm**  
**For black skin**  
 (black hair removal)

# • *Cooling effect* •

The handle is frosted for one minute,  
making your treatment more comfortable and painless



Suitable for hair removal on any part of the body,  
Such as arms, legs, face, armpits, back, chest, etc.







### 14 Android Screen

1. Three wavelength diode laser.
2. Golden laser bars from German or USA improved, 40,000,000+ longer lifespan.
3. Safe, Fast, Painless, permanent
4. For all skin and hair style hair removal
5. 14.0 inch true color touch screen with 6 skin colors.



808V30  
 800 16----8  
 4 14  
 808nm 755 nm 808nm 1064nm  
 50  
 10~150 j/cm2  
 1-10  
 TEC  
 3500  
 12 \* 20 35 \* 12  
 110 50 / 220 60 /  
 95  
 105

! 100% 100% 100% 100% 100% 100%



□□□□ 24 □□□□□□!!