



808+ND Nd yag




1. 808nm 800W 1 2 808nm Nd yag laser hair removal machine for hair removal
2. 808nm 40-10 808nm Nd yag laser hair removal machine for hair removal
3. Nd yag: 1064 808nm Nd yag laser hair removal machine for hair removal





□□□□ □□□□□□

Three wavelengths work together




Suitable for hair removal on any part of the body,
Such as arms, legs, face, armpits, back, chest, etc.

[illegible]



Before

After




Before



After



Before



After

5 therapeutic Heads

■ 532 & 1064: removing tattoo, eyeliner and lip line

■ 1320: black-faced doll whitening and whitening skin

■ Adjustable 532 & 1064: removing large-area tattoos



Adjustable
532nm



Adjustable
1064nm



Black doll
1320nm



Fixed
532nm




Fixed
1064nm

Nd yag:


1064 5 532nm/1064nm 1320 1320nm.

Working Principle



1. 00000 0000 0000 000 6 0000 00000 000/000.
2. 000 00000 0000 00000000.
3. 000000 00000 OEM 00000/00000) 000000...

System Design



808 Mode:Operation interface

Laser Mode:Tattoo removal

1111

808 0000 0000nd

□ □ □ □ □ □

□□□□ □□ □□□□□□ □□□ □□□□ Nd yag□ 808 □□□□□ □□□□

--	--	--	--	--	--	--	--

2000 □□□

SHR

1-10 □□□□

808 □□□□ □□□□□□

12 * 20 35 * 12

Nd yag

□□□□ 5 □□ □□ □□□□□□□□ □□□□ □□□□

□ □ □ □ □

10-50 J/cm²

□ □ □ □ □ □ □ □ □ □

1-10

□ □ □ □ □ □ □ □ □ □ □ □

-21

□ □ □ □ □ □ □ □ □ □ □ □ □

[illegible]

--	--	--	--	--	--	--	--

液晶 LCD 12 色 TFT

5/5/2016

220v/50hz 110 □□v/60hz

116*60*61 □□□ □□□□□

[illegible]

90 □□□□□□



15 Years Laser Beauty Device Manufacturer

Make your beauty business easier



1. Weifang Sunshinekj electronics Co., Ltd (简称为:MLKJ) 是一家专业从事美容仪器研发、生产、销售的高新技术企业。公司拥有先进的生产设备和专业的技术团队，致力于为客户提供高品质的美容仪器。公司成立于2010年，经过15年的发展，已成为行业内知名的制造商。公司占地面积约200亩，拥有员工500余人。

Premium OEM Factories

High-performance manufacturing capacity
R&D capability for customization
Professional certifications and approvals



Product Customization Design



Program Debugging



Batch Production



Production and Processing



Machine Debugging



Fine and Safe Packaging

Packing

Safe and thoughtful packaging service



Tight packaging

The machine shall be made of waterproof materials and packaged

**Anti collision foam board
inside aluminum box**



3-5 business days delivery

Professional guide:

24 Hours Professional online customer service