



IPL A6
 For hair removal
 & skin rejuvenation

1. 8.4 inch LCD true color touch screen
 2. IPL handle
 3. Emergency Switch
 4. Key Switch
 5. 30000-150000 pulses
 6. 50 * 15 cm treatment area
 7. 8.4 inch TFT LCD screen
 8. 30000-150000 pulses
 9. 50 * 15 cm treatment area
 10. 30000-150000 pulses



8.4 inch LCD true color touch screen

Elight Handle Design



Specification

Optional Spot Size:
15*50mm

Imported UK lamp

Long shots time:
150,000--300,000 times

7filters:
420/510/560/585/640/690/755nm

Super cooling system



□□□□ □□□□□ □ □□□□□ □□□□ □□□□ □□□□ □□□□ □□□□.



□□□□ **8.4** □□□□ □□□□ □□□□ □□□□ □□□□□□□□
1. □□□□□□ □□□□□□ □□□□□□ 8.4 □□□□ □□□□ □□□□ □□□□

- .2 6 2
- .3
- .4 OEM (OEM/...)

Screen interfac

Professional Screen, Easy operation



Main Menu
8.4 inch true color big touch screen
Super cool touch Experience.



IPL mode:
5 options for skin treatment




IPL mode:
operation interface



Multi-language screen:
6 languages for your choice



System setting



System setting

- 1. 6 languages
- 2. 8.4 inch touch screen
- 3. 5 options for skin treatment
- 4. 5 options for skin treatment
- 5. 5 options for skin treatment
- 6. 5 options for skin treatment
- 7. 5 options for skin treatment
- 8. 5 options for skin treatment
- 9. 5 options for skin treatment
- 10. 5 options for skin treatment

IPL: 50 * 15
420/510/560/585/640/690/755nm
150000-30000
8.4
TEC 1200W 1 3
2
AU 110 220
30
220V
220V

Multi-angle display



Left view



Front view



right elevation