



Free to be yourself

A minute of painless freezing hair removal,
Feeling the comfort and coolness that
has never been seen before.

14-inch screen

2 year warranty + work 24 hours

One minute cooling -21°C



Best **TEC Cooling** system
hair remover laser

* 1000W 1200W 1600W Dilas (1064 808 755 nm) . 35 * 12 cm

. 1064 808 755 nm 1064 808 755 nm 3 40 cm *
1064 808 755 nm 1064 808 755 nm 3 40 cm *

1000W 1200W 1600W 1064 808 755 nm 35 * 12 cm
12 * 20 cm 1064 808 755 nm 35 * 12 cm

350g lightweight **handle**, more ergonomic



Available in **black or white**




High-quality
laser bars
imported from
USA

1000/1200/1600ww high power



Fast hair removal



⌚ 10bar
1000W




⌚ 12bar
1200W



⌚ 16bar
1600W

For all skin types



755nm / 808nm / 1064 nm




0000 0000 0000 000000 1064 808 808 755 000000 000

* 00 000 00000000 000000 000 00000000 00000000 0000 0000
000 000 000 000 000 000000 000 *

000000 000000 00 000 000 000 *

000000 000



1 minute
and you're done

35mm {

FASTER

12 * 20mm 35 * 12 00mm 00 000 000000 000 0000 000000 0000 00000000
3 --- 5 000000 000000 000 000 000 00 00000 000000 000 00 000000

The new 14-inch screen is clear
easy to operate.



OEM/ODM SEVRICE

3D LOGO with luxurious texture.