

NEW ! Technology



Free to be yourself

1 minute of painless hair removal,
Feeling the comfort and coolness that
has never been seen before.

14-inch screen

2 year warranty + work 24 hours



0000 0000 0000 000000 000000

1.) 0000 000000 00 0000 0 000000 0000 000000

000 0000 000000 0000 000 00 0000 0 000000 00 000000 000 0000 000000 00000000 (.2.

1 minute
and you're done

35mm {

FASTER

1200 12 / 1000 10 20 * 12

1600 16 35 * 12


Handle Details

Three Wavelengths Work Togher




12*20nm

755nm Laser
808nm Laser
1064nm Laser



12*35nm


755nm Laser
808nm Laser
1064nm Laser



Best **TEC Cooling** system hair remover laser



በግልጽ ለሚታወቅ ምርጫ ማድረግ ማለት ማለቱን ማሳወቅ ነው።



3 1000w 1200w 1600w
755 (nm) 808nm / 1064nm (nm)

Stuit to any color of skin



Application:


Elight for Skin Rejuvenation, Skin Tightening, Wrinkle Removal, Acne Removal, Pigment Removal, Vascular Removal, Breast Lifting, Age Spot Removal etc.

808 Hair Removal treatment pictures



The new **14-inch 4K** screen

Support system customization



主要規格

波長	755 nm 808nm 1064nm
光斑大小	16 / 12 / 10 mm 光斑大小
脈衝寬度	50 μs
脈衝頻率	1-14 Hz 脈衝頻率
光斑大小	808nm / 755nm / 1064nm
光斑大小	12 * 20mm ² / 12 * 35mm ²
脈衝寬度	808nm: 40000-1000000 μs
脈衝頻率	10-150 J / cm ² 150 J / cm ² (脈衝頻率)
脈衝寬度	40 ~ 800 μs 脈衝寬度
脈衝頻率	1.0-10 Hz
脈衝寬度	TEC 脈衝寬度
脈衝寬度	1000w / 1200w / 1600w
脈衝寬度	2000 μs
脈衝寬度	220 μs 60 / 110 μs 50 / 110 μs
脈衝寬度	-10 ~ 3 μs 脈衝寬度
脈衝寬度	27 ~ 31 μs 脈衝寬度

□□□□ □□□□ □□□□ AC220V / 110V 50 ~ 60 □□□□
□□□□□□ □□□ 95 □□□□□□□□
□□ □□□□□□□□

1. Weifang Sunshinekj electronics Co.□ Ltd (□□□□: MLKJ) □□□ □□□□□ □□ □ □□ □□□□ □□□□□
□□□ □□ □□□□□□ □□□□□□ □□□□ □□ □□□ 13 □ □□□ □□ □□□□□□ □□□□□□□ □□□□□ □□□□□

About Us

We Are 13 Years

Professional high-tech beauty equipment manufacturer in China.

潍坊明亮电子有限公司

坚守客户价值不动摇·让客户满意
This firmly to customer's value to make them feel satisfied

坚守员工价值不动摇·让员工成长
Hold Fast to employees' value to let them develop



Mingliangkj in 2007, Through 13 years ,we have built reliable Production ,Quality Control ,Warehousing and Sale&Service department.

Products around world ,including Europe ,North America, Asia and so on .more than 600 clients in more, than 100 countrys all over the world



NEW



Research and Development

We have professional Production R & D department.
From design research and development to production, every step is strictly checked to ensure product quality.



CAD and PCB drawing



Electrical schematic diagram and preparation procedures



Ammeter test



Install the motherboard



Assemble the hardware



Leave the factory after passing the inspection



Packing And Delivery

1



Print Logo



Check accessories before packing

2



Wiping and Wrapping machine



Rigorous inductive packing

3



Reminder identification



Fast delivery